








Schematic(Shorting)

NOTE:
1.Operating force:200±100gf

⑤	Knob	—	1	NYLON	Black	—
④	Cover	—	1	SUS	—	—
③	Base	—	1	LCP	Black	—
②	Contact Clip	—	2	Beryllium bronze	Ag Clad	—
①	Terminal	—	10	Phosphor bronze	Ag Plated	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	LIUCAN	2022.12.6				
CHECKED			TITLE:		TOGGLE SWITCHS	
APPROVALS			PART NO.		K3-2411S-F1	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15	±2°	DRAWING NO.	PROJ: 
		~ 5	±0.10			
						SHEET 1 OF 1

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.