








MATERIALS

1. HOUSING : LCP, UL 94V-0, BLACK.
2. TERMINAL : C2680, T=0.20mm,
PLATING : GOLD PLATED ON CONTACT AREA,
TIN PLATED ON SOLDER TAILS.
3. SHELL : STAINLESS STEEL, T=0.30mm,
PLATING : 50u" NICKEL MIN PLATING.






SPECIFICATION

1. CURRENT RATING : 0.5 A. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE :
500V AC R.M.S. FOR 1 MINUTE.
3. INSULATION RESISTANCE : 100M Ω MIN. AT 500V DC.
4. CONTACT RESISTANCE : 30m Ω MAX.
5. OPERATING TEMPERATURE : -25°C TO +85°C.
6. INSERTION FORCE : 4.5Kgf MAX.
7. WITHDRAWING FORCE : 1Kgf ~ 4Kgf.
8. DURABILITY : 10000 CYCLES.
9. SOLDERING HEAT RESISTANCE REFLOW SOLDERING
260°C/5sec.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X $\pm$ 0.30 X.XX $\pm$ 0.25 X.XXX $\pm$ 0.15 X' $\pm$ 2" X.X" $\pm$ 0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI2.1 A TYPE SMT 弹片加高翻边 有卡点	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW175-HDMI A19-108B	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO: HYC-2606161109	
			SHEET NO.	1 OF 1



TAPE & REEL PACKAGE : SIZE

- 1. REEL : $\phi 380$ X 44 mm
- CARTON : L=400mm, W=400mm, H=380mm

QUANTITY

- 1. 300 PCS PER REEL.
- 2. 7 REEL PER CARTON (2100 PCS PER CARTON).

MATERIALS

- 1. CARRIER TAPE: POLYSTYREN (PS)
- 2. COVER TAPE: POLYSTYREN (PS)
- 3. REEL: POLYSTYREN (PS)
- 4. APPLICABLE DOCUMENTS : EIA-481-C



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2^{\circ}$ X.X' $\pm 0.5^{\circ}$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	
SCALE:1:1	SIZE: A4		SHEET NO.	1 OF 1