





ROHS



NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance: $\leq 20 \text{ m}\Omega$
- 4.Insulation resistance: $\geq 500 \text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		插拔式接线端子PIN距3.81（2P）直插（带螺母）	REV.	A
30-150	±0.35	ANGLE	PART NO.		LAIL-PTB3.81-2P-GN-02S-ZC	UNITS	mm
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG.NO.		Projection 		