






PCB Layout(Pattern side)



Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Contact Resistance: $\leq 100\text{m}\Omega$
- 3.Insulation Resistance: $\geq 100\text{m}\Omega$
- 4.Life : 100,000 Cycles
- 5.Waterproof level: IP67



Circuit Diagram

NO.1		
PART NO	H	L
A	4.3	2.95
B	4.5	3.45
C	5.0	3.95
D	5.5	4.45
E	6.0	4.95
F	6.5	5.45
G	7.0	5.95
H	7.5	6.45
I	8.0	6.95
J	8.5	7.45
K	9.0	7.95
L	9.5	8.45
M	10.0	8.95

NO.2	
PART NO	vigor
3	160±40
4	250±40

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑥	Waterproof pad	—	1	silica gel	Black	—
⑤	Cover	—	1	Brass	Tin Plated	—
④	Keystoke	—	1	PPA	Black	—
③	Contact	—	1	F.Ag/SUS	Plating silver	—
②	Base	—	1	PPA	Black	—
①	Terminal	—	2	Brass(0.3t)	Plating silver	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®		
DRAWN	LIUCAN	2021.9.23					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1839AP-□□SW-□□		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.	_____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.