







0.10 (16PIN SMT)

⑧	1	下端子	铜合金C7025 TM03	镀金3U"
⑦	1	上端子	铜合金C7025 TM03	镀金3U"
⑥	1	I/M	PA46	黑色
⑤	1	中隔片	不锈钢SUS301	水洗
④	1	EMI	不锈钢SUS304	电镀镍300"
③	1	内铁壳	不锈钢SUS316	水洗
②	1	密封圈	液态硅胶成型	黑色 NJSILTMNJ-1005-50A/B
①	1	外铁壳	不锈钢304	电镀镍50U"
⑨	1	胶水	黑色环氧胶	
序号	数量	零件名称	材料	镀层




深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." ± 2 " X.X" ± 0.5 " UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 防水母座16P 板上垫高CH4.8mm 带防水胶圈	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW604-USBC16-480B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2412021032
			SHEET NO.	1 OF 1



RECOMMENDED PCB LAYOUT(TOP VIEW)

PCB THICKNESS 1.72±0.05MM



Notes:

1. ELECTRICAL characteristics:

1-1. Dielectric withstance: 500V AC/1minute.

1-2. Current rating:

Vbus and GND contact: ≥1.25A/pin, Paralleled for a total of 5A Min

Other contacts: ≥0.25A/pin

1-3. Initial LLCR 40mΩ max, after test Δ10mΩ max:

40mΩ MAX. FOR VBUS, GND AND OTHER CONTACTS,

50mΩ MAX. FINAL AFTER TEST.

1-4. Insulation Resistance: 1000MΩ Min

2. Mechanical characteristics

2-1 Insert force: 5~20N MAX.

Withdraw force: 8~20N, after test: 6~20N

2-2 Durability: 10000 cycles min

2-3 Laser point: Height < 0.05mm, Pulling force > 50N

3. Environment characteristics

3-1 Operating temperature: -40~+85°C

3-2 Salty spray: 48 hours (EIA-364-26B-B)

4. Burr: 0.05mm MAX.

5. Tape and reel packing satisfy EIA-364-481 standard

Pin	Signal	Description	Mating Sequence	Description	Signal	Pin
2	A1	GND	First	Ground return	GND	B12
/	A2	TX1+	Second	/	RX1+	B11
/	A3	TX1-	Second	/	RX1-	B10
4	A4	VBUS	First	Bus Power	VBUS	B9
6	A5	CC1	Second	Sideband Use (SBU)	SBU2	B8
8	A6	Positive half of the USB 2.0 differential pair-Position 1	Second	Negative half of the USB 2.0 differential pair-Position 2	D-	B7
9	A7	Negative half of the USB 2.0 differential pair-Position 1	Second	Positive half of the USB 2.0 differential pair-Position 2	D+	B6
11	A8	SBU1	Second	Configuration Channel	CC2	B5
13	A9	VBUS	First	Bus Power	VBUS	B4
/	A10	RX2-	Second	/	TX2-	B3
/	A11	RX2+	Second	/	TX2+	B2
15	A12	GND	First	Ground return	GND	B1



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.X' ±2" X.X" ±0.5'	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	USB TYPE C 防水母座16P 板上垫高4.8mm 带防水胶圈
	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	HYCW604-USBC16-480B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	HYC-2412021032
		SHEET NO.	1 OF 1