





ROHS

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |



NOTE:  
1.Rated voltage: 300V AC.DC  
2.Rated current: 15A AC.DC  
3.Contact Resistance: 20mΩ Max  
4.Insulation Resistance: 500MΩ Min  
5.Withstanding Voltage: 2000V AC/minute  
6.Ambient temperature: -40℃to+105℃  
7.Material: Nylon UL94V-0

|                  |       |                                       |                           |                             |       |            |                                                                                       |
|------------------|-------|---------------------------------------|---------------------------|-----------------------------|-------|------------|---------------------------------------------------------------------------------------|
| 5                | 盖板    | PA66 UL94V-0                          | 1                         | 绿色                          |       |            |                                                                                       |
| 4                | 压线框   | 黄铜                                    | 2                         | 镀镍                          |       |            |                                                                                       |
| 3                | 夹片    | 磷青铜                                   | 2                         | 镀镍                          |       |            |                                                                                       |
| 2                | 基座    | PA66 UL94V-0                          | 1                         | 绿色                          |       |            |                                                                                       |
| 1                | 螺钉    | 钢                                     | 2                         | 镀锌                          | M2. 5 |            |                                                                                       |
| 序号               | 名称    | 材质                                    | 数量                        | 电镀/颜色                       | 备注    |            |                                                                                       |
| COSTOMER DRAWING |       | LAILIAN 深圳市莱联电子有限公司                   |                           |                             |       |            |                                                                                       |
| DRAWING          |       | SHENZHEN LAILIAN ELECTRONICS CO., LTD |                           |                             |       |            |                                                                                       |
| CHECK            |       |                                       |                           |                             |       |            |                                                                                       |
| APPROVAL         |       |                                       |                           |                             |       |            |                                                                                       |
| TOLERANCES ARE   |       | TITLE                                 |                           | 插拔式接线端子PIN距5.08 (2P) 公插头带螺钉 | REV.  | A          |                                                                                       |
| 30-150           | ±0.35 | PART NO.                              | LAIL-PTB5.08-2P-GN-01S-MC | UNITS                       | mm    |            |                                                                                       |
| 10-30            | ±0.2  |                                       |                           |                             |       |            |                                                                                       |
| 5-10             | ±0.15 |                                       |                           |                             |       |            |                                                                                       |
| 0-5              | ±0.1  |                                       |                           |                             |       |            |                                                                                       |
| ANGLE            |       | DWG.NO.                               |                           |                             |       | Projection |  |
| ±3°              |       |                                       |                           |                             |       |            |                                                                                       |