





RECOMMEND PCB LAYOUT
TOLERANCE: ±0.05
TOP VIEW



NOTES:

1. HOUSING: LCP (UL94V-0), BLACK.
2. TERMINAL: COPPER ALLOY,
GOLD PLATED ON CONTACT AREA,
TIN PLATED ON SOLDER TAILS.
NICKEL PLATED OVERALL.
3. SHELL: STAINLESS STEEL, T=0.30mm,
NICKEL PLATED OVERALL.

SPECIFICATION

1. CURRENT RATING: 0.5A MAX .
2. DIELECTRIC WITHSTANDING VOLTAGE:
500V AC R.M.S. FOR ONE MINUTE.
3. INSULATION RESISTANCE: 100MΩ MIN.AT 500V DC.
4. CONTACT RESISTANCE: 30mΩ MAX.
5. OPERATING TEMPERATURE: -25°C TO +85°C.
6. DURABILITY: 10000 CYCLES.
7. MATING FORCE: 4.5kgf MAX.
8. UNMATING FORCE: 1.0kgf MIN.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: DP 侧插母座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW38-DP20-260B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2308101653
			SHEET NO.	1 OF 1

