



Typical Specifications :

1. Rating : DC 15V 20mA
2. Operating Force : 160 ± 50 gf
3. Life: 300,000 Cycles Min.

⑤	Knob	—	1	Nylon	Black	—
④	Dust cover	—	1	KAPTON FILM	White	—
③	Terminal	—	2	Phosphor Bronze	Plating silver	—
②	Contact	—	3	F.Ag/SUS	Plating silver	—
①	Base	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2025.3.9					
CHECKED					TITLE:	TACT SWITCHS	
APPROVALS					PART NO.	K2-1837FR-C3DW-06	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2°	DRAWING NO.	_____		SHEET 1 OF 1

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO