









PCB WELDING DIMENSIONS



NO.1	
PART NO	H
A	1.9
B	2.5

SPECIFICATION

- 1.Rating:DC 32V 50mA Max / DC 20mV 1mA Min
- 2.Contact resistance:100mΩ MAX
- 3.Insulation resistance:100MΩ Min,100V
- 4.Dielectric strength:250V AC/min
- 5.Travel:0.20±0.1mm
- 6.Operating force: 300gf±60gf
- 7.Operating life: ≥5X10⁴cycles
- 8.Operating temp: -40℃to+85℃
- 9.Storage temp: -40℃to+85℃
- 10.Protection grade:IP40

⑥	TERMINAL		1	BRASS	Ag-PLATED	_____
⑤	HOUSING	—	1	PA	BLACK	_____
④	CONTACT FORM	—	2	SUS301	Silver coated	_____
③	TAPE	—	1	GATHERS THE IMIDE	YELLOW	_____
②	STEM	—	1	PPA	BLACK	_____
①	COVER	—	1	SUS304	_____	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE			
DRAWN	LIANG		2026.03.12			
CHECKED					TITLE:	TACT SWITCHS
APPROVALS					PART NO.	K2-2842SN-□6DW-01
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10				
			±2'	DRAWING NO.	_____	SHEET 1 OF 1

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.