

# SOT-23 Plastic-Encapsulate Transistors

## MMBT3904

NPN Transistors


### Features

- Complementary to MMBT3906

Marking: 1AM

### Maximum Ratings (T<sub>a</sub>=25°C unless otherwise noted)









| Symbol           | Parameter                               | Value     | Unit |
|------------------|-----------------------------------------|-----------|------|
| V <sub>CB0</sub> | Collector Base Voltage                  | 60        | V    |
| V <sub>CEO</sub> | Collector Emitter Voltage               | 40        | V    |
| V <sub>EBO</sub> | Emitter Base Voltage                    | 6         | V    |
| I <sub>c</sub>   | Collector Current                       | 200       | mA   |
| P <sub>c</sub>   | Collector Power Dissipation             | 200       | mW   |
| T <sub>j</sub>   | Junction Temperature                    | 150       | °C   |
| T <sub>stg</sub> | Storage Temperature                     | -55 ~ 150 | °C   |
| R <sub>θJA</sub> | Thermal Resistance, Junction to Ambient | 625       | °C/W |




### Electrical Characteristics (T<sub>a</sub>=25°C unless otherwise specified)

| Symbol               | Parameter                            | Test Conditions                                      | Min | Typ | Max  | Unit |
|----------------------|--------------------------------------|------------------------------------------------------|-----|-----|------|------|
| V <sub>(BR)CBO</sub> | Collector-base breakdown voltage     | I <sub>C</sub> = 10μA, I <sub>E</sub> = 0            | 60  |     |      | V    |
| V <sub>(BR)CEO</sub> | Collector-emitter breakdown voltage  | I <sub>C</sub> = 1mA, I <sub>B</sub> = 0             | 40  |     |      | V    |
| V <sub>(BR)EBO</sub> | Emitter-base breakdown voltage       | I <sub>E</sub> = 10μA, I <sub>C</sub> = 0            | 6   |     |      | V    |
| I <sub>CBO</sub>     | Collector cut-off current            | V <sub>CB</sub> = 60V, I <sub>E</sub> = 0            |     |     | 100  | nA   |
| I <sub>CEX</sub>     | Collector cut-off current            | V <sub>CE</sub> = 30V, V <sub>EB(off)</sub> = 3V     |     |     | 50   | nA   |
| I <sub>EBO</sub>     | Emitter cut-off current              | V <sub>EB</sub> = 5V, I <sub>C</sub> = 0             |     |     | 100  | nA   |
| h <sub>FE(1)</sub>   | DC current gain                      | V <sub>CE</sub> = 1V, I <sub>C</sub> = 10mA          | 100 |     | 300  |      |
| h <sub>FE(2)</sub>   |                                      | V <sub>CE</sub> = 1V, I <sub>C</sub> = 50mA          | 60  |     |      |      |
| h <sub>FE(3)</sub>   |                                      | V <sub>CE</sub> = 1V, I <sub>C</sub> = 100mA         | 30  |     |      |      |
| V <sub>CE(sat)</sub> | Collector-emitter saturation voltage | I <sub>C</sub> = 50mA, I <sub>B</sub> = 5mA          |     |     | 0.3  | V    |
| V <sub>BE(sat)</sub> | Base-emitter saturation voltage      | I <sub>C</sub> = 50mA, I <sub>B</sub> = 5mA          |     |     | 0.95 | V    |
| f <sub>r</sub>       | Transition frequency                 | V <sub>CE</sub> =20V, I <sub>C</sub> =10mA, f=100MHz | 300 |     |      | MHz  |
| C <sub>ob</sub>      | Collector output capacitance         | V <sub>CB</sub> = 5V, I <sub>E</sub> = 0, f = 1MHz   |     |     | 4    | pF   |
| t <sub>d</sub>       | Delay time                           | V <sub>CC</sub> = 3V, V <sub>BE(off)</sub> = -0.5V,  |     |     | 35   | ns   |
| t <sub>r</sub>       | Rise time                            | I <sub>C</sub> = 10mA, I <sub>B1</sub> = 1mA         |     |     | 35   | ns   |
| t <sub>s</sub>       | Storage time                         | V <sub>CC</sub> = 3V, I <sub>C</sub> = 10mA,         |     |     | 200  | ns   |
| t <sub>f</sub>       | Fall time                            | I <sub>B1</sub> = I <sub>B2</sub> = 1mA              |     |     | 50   | ns   |

# Typical Characteristics



## SOT-23 Embossed Carrier Tape




### Packaging Description:


SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

| Dimensions are in millimeter |      |      |      |       |      |      |      |      |      |      |  |
|------------------------------|------|------|------|-------|------|------|------|------|------|------|--|
| Pkg type                     | A    | B    | C    | d     | E    | F    | P0   | P    | P1   | W    |  |
| SOT-23                       | 3.15 | 2.77 | 1.22 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |  |

## SOT-23 Tape Leader and Trailer



## SOT-23 Reel(S)



| Dimensions are in millimeter |         |       |             |        |        |       |            |            |
|------------------------------|---------|-------|-------------|--------|--------|-------|------------|------------|
| Reel Option                  | D       | D1    | D2          | G      | H      | I     | W1         | W2         |
| 7"Dia                        | Ø178.00 | 54.40 | <b>13.8</b> | R78.00 | R25.60 | R9.35 | <b>6.6</b> | <b>8.8</b> |

| REEL     | Reel Size | Box        | Box Size(mm)       | Carton      | Carton Size(mm)    | G.W.(kg) |
|----------|-----------|------------|--------------------|-------------|--------------------|----------|
| 3000 pcs | 7 inch    | 45,000 pcs | <b>210X208X203</b> | 180,000 pcs | <b>440X440X227</b> |          |