







 HONGAU	深圳市华宇创精密电子有限公司
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY : 陈一鸣 DATE : 2014-02-23
 UNIT: mm [inch]	PART NAME: HDR15母 架高 塑胶支架 横叉 铆锁
	CHECKED BY: 马跃 DATE : 2014-02-23
 UNIT: mm [inch]	PART NO. HXCW259-VGA15B-316B
	MOLD NO.
 UNIT: mm [inch]	APPROVED BY: 邱敏 DATE : 2014-02-23
	DRAW NO: HXC-2606111445
SCALE: 1:1 SIZE: A4	SHEET NO. 1 OF 1



BRACKET: PA66,PANTONE BLACK,UL94V-0 RATED.

SCREW: PLATED NICKEL 120u" Min. PLATED Cu 80u" ALLOVER.

CONTACT CURRENT RATING:2 AMP.
DIELECTRIC WITHSTANDING VOLTAGE:AC 500V.
INSULATION RESISTANCE:1000 MEGAOHMS MIN.AT DC 500V
CONTACT RESISTANCE:30 MILLIOHMS MAX.

4.ENVIRONMENTAL:TEMPERATURE RANGE -20°C TO +85°C

MATING FORCE:4.5 KG(FINITIAL).
UNMATING FORCE:3.5 KG(FINITIAL).
CONTACT RETENTION TO HOUSING:0.5 KG(MIN);
DURABILITY:1000MATING CYCLES
ENDURANT TWISTING FORCE OF THE SCREW:5.5 KG-CM MAX.