


1. External Dimensions (Unit:m/m)



Type	A	B	C	D Typ.	E Typ.	F Typ.	G Typ.	H Typ.	Q'TY/Reel
AAPS0855	8.3±0.3	9.2Max	5.5Max	3.0	1.6	9.4	3.7	4.7	500

2. Part Number Code

AAPS	08	55	M	4R7	A
Series Name	Dimensions: L*W	Dimensions: H	Tolerance ±20%	Inductance	Materials

3. Electrical Characteristics

Part Number	Inductance (uH)	Test Conditions	DC Resistance (mΩ) Max	DC Current Irms(A)Typ.	DC Current Isat(A)Typ.	SRF/MHz Typ.
AAPS0855M4R7A	4.7	100KHz/1V	15.6	9.2	15	16

Notes:

- 1) AEC-Q200 qualified.
- 2) All test data is referenced to 25°C ambient.
- 3) Absolute maximum voltage 100VDC.
- 4) Operating temperature range -55°C to +155°C, (Including self - temperature rise).
- 5) Irms :DC current(A) that will cause an approximate ΔT of 40°C.
- 6) Isat :DC current(A) that will cause I_o to drop approximately 40%.
- 7) The part temperature(ambient + temp rise) should not exceed 155°C under worst case operating conditions. Circuit design and other cooling provisions all affect the part temperature, part temperature should be verified in the end application.