


1. DVI
- 1.1 Voltage: 40 VAC(RMS) Max.
- 1.2 Current Rating: 1.5 Ampere per Contact
- 1.3 Contact Resistance(UPPER): 30 Milliohms Max.
- 1.4 Insulation Resistance: 1000 Megohms Min.
- 1.5 Dielectric Withstanding Voltage: 500V DC(RMS)
- 1.6 Total Mating Force: 4.5 Kgf Max.
- 1.7 Total Unmating Force: 1.0 Kgf Min.
- 1.8 Operating Temperature: -55°C to +85°C
- 1.9 Screw Locking Force: 2.5~3.0 Kgf.
- 2.0 Screw Back Force: 1.0 Kgf Min.

1. MATERIAL:
Housing:LCP Halogen-free, UL 94V-0, Color:Black.
Bracket:LCP Halogen-free, UL 94V-0, Color:Black.
Terminal:Brass.
Shell:SPCC.
Shield:SUS 304.
Boardlock:SPCC.
Rivet:Brass..
2. FINISH:
Terminal:Gold Plated over 30u" min Nickel at
Contact Area. 100u" min Tin Plated
over 30u" min Nickel at Solder Ared.
Shell:Nickel Plating 80u" min. Overall.
Shield:Solderable Nickle Plating 80u" min. Overall.
Boardlock:Tin Plating 100u" min. over 80u" min.
Nickel Overall.
Rivet:Nickel Plating 50u" min. Overall.
3. This Product is HALOGEN-FREE & RoHS
Compliance Product.



COMPONENT SIDE VIEW(TOLERANCE:±0.05)
INSPECTION DIMENSION:(A)~(I)

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.* $\pm 2^{\circ}$ X.X* $\pm 0.5^{\circ}$		DRAWN BY : DATE : 陈一鸣 2014-02-23 CHECKED BY: DATE : 马跃 2014-02-23	
 UNIT: mm [inch]		PART NAME: DVI24+1 悬空型带塑胶支架	
		PART NO. HYCW52-DVI25-303B	MOLD NO.
APPROVED BY: DATE : 邱敏 2014-02-23		DRAW NO: HYC-2606111505 SHEET NO. 1 OF 1	