





Poles	Dimenslons(mm) A
2*02	5.08
2*03	7.62
2*04	10.16
2*05	12.70
2*06	15.24
2*07	17.78
2*08	20.32
2*09	22.86
2*10	25.40
2*12	30.48
2*14	35.56
2*16	40.64
2*20	50.80
2*21	53.34
2*24	60.96
2*25	63.50



Recommended P.C.B
Layout(±0.05)

Technical Data
Pin(outer sleeve):Brass,machined CuZn38Pb2
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating pin Ø:0.60/0.48mm
Mechanical life:min 500cycles
Contact resistance:max 10mΩ
Dielectric strength:min 1000V RMS
Operating temperature:-40°C to+105°C
Soldering temperature:+255°C

X5621W V-2x14-C1524 D1196-1196

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series.N0.
- ② Category : W-Wafer
- ③ Welding Board Angle : V-Straight 180°
- ④ Row No-Pin No:2*XX-03,04,05,06,07,08,09,10,12,14,16 20,21,24,25
- ⑤ Plastic Height :C=15.24mm
- ⑥ Pin Length :D:1196=11.96mm;1000=10.0mm;1220=12.20mm;
- ⑦ 1196:Type1196

X5621WV-2x14-C1524D1196-1196	PPS 94V-0	Brass	Tin Gold 1u"	X5621F
PART N0	Material	Material(Terminal)	Finish(Terminal)	Mates With XKB Pin Header

							DSND		DATE		SCALE: N/A	MODEL TYPE:				
					ANGLAR	±5°	DWN		DATE		VIEW: 	2.54mm BTB Style Connector				
Δx					L ≤ 4	±0.2						PART NO.:				
Δx					4<L ≤ 16	±0.3	CHKD		DATE		UNIT: mm/in	X5621WV-2x14-C1524D1196-1196				
Δx					16<L ≤ 63	±0.4						DWG NO.:				
MARK	DESCRIPTION				DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4	X-X5621WV-2x14-C1524D1196-1196			
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																
												WEIGHT	SHEET	REVISION		
												1.0g	1/1	A0		