



1. Configuration & Dimensions : (Unit:mm)



SYMBOL	A	B	C	D	E	F	Q'Ty/Disc
ADT130705	17.5Max	8.0Max	3.05±0.35	0.9±0.1	1.5Max	5.0Ref	200

2. Electrical Schematics



3. Part Number Code

ADT 130705 X 351 -BW
 A B C D E

A: Series Name Coated Amorphous Chokes
 B: Dimensions(mm) 130705: 17.5*8.0 Max
 E: Tolerance X: Min
 F: Inductance 351=350uH
 E: Internal controls

4. Electrical Characteristics

Part Number	Inductance (uH)Min.	Test Frequency (Hz)	DC Resistance (mΩ)Max.	L1A (uH)Min.
ADT130705X351-BW	350.0	1KHz/0.3V	15.0	50.0

Notes:

- 1) All test data is referenced to 25°C ambient.
- 2) Operating temperature range -40°C to +125°C.

5. Material List