




RoHS

REV.	ECN. #	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02



NOTES:

1. MATERIAL:

1.1 HOUSING: LCP UL94V-0; COLOR: BLACK

1.2 TERMINAL: C2680

1.3 SHELL: SUS304

1.4 INNER SHELL: SUS304

1.5 MID PLATE: SUS301

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;

G/F PLATED ON SOLDER AREA;

Ni 30u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 50u" MIN. PLATED OVERALL

2.3 MID PLATE: CLEANING.

3. ELECTRICAL SPECIFICATION:

3.1 RATED CURRENT: VBUS AND GND PIN 3.0A;

Other pin 0.25A

3.3 CONTACT RESISTANCE: 40mΩ MAX(INITIAL). 50mΩ MAX (AFTER).

3.4 INSULATION RESISTANCE: 100MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC R.M.S.

4. MACHINERY SPECIFICATION:

4.1 MATING FORCE: 5N~20N.

UNMATING FORCE: 8N~20N. (AFTER TEST: 6N~20N).

4.2 DURABILITY: 10000 CYCLES MIN.

5. ENVIRONMENTAL SPECIFICATION



5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;

HUMIDITY 80% R.H MAX

5.2 SALT SPRAY: 24H

6. SOLDER ABILITY: 245±5°C, 5±0.5s

7. IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.



Recommended P.C.B. Layout
Unspecified tolerance: ±0.05
(Top view)

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBilal Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	TYPE C 6PIN 板上7.30防水7级两脚插 (点胶款)	DR		
PART NO.	1043115242	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	