





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.19	阿树



Specifications:

规格:

Voltage rating:50V AC/DC

额定电压: 50V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range: -40°C $-$ $+125^{\circ}\text{C}$

温度范围: $-40^{\circ}\text{C}-+125^{\circ}\text{C}$

Insulation resistance:100MΩ min

绝缘电阻: 100MΩ Min

Contact resistance:50mΩ Max

接触电阻: 50mΩ Max

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x05	5.00	9.50	8.70	2x13	15.00	19.50	18.70
2x06	6.25	10.75	9.95	2x14	16.25	20.75	19.95
2x07	7.50	12.00	11.20	2x15	17.50	22.00	21.10
2x08	8.75	13.25	12.45	2x16	18.75	23.25	22.45
2x09	10.00	14.50	13.70	2x17	20.00	24.50	23.70
2x10	11.25	15.75	14.95	2x18	21.25	25.75	24.95
2x11	12.50	17.00	16.20	2x19	22.50	27.00	26.20
2x12	13.75	18.25	17.45	2x20	23.75	28.25	27.45

PART NO.:

X1254 W V S - 2xXX A - LP XX
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
②Category:W—Wafer
③Welding Board Angle:V—Stright 180°
④Welding way :S—SMT
⑤Row No.Pin No:2xXX~2x05~2x20 Pin
⑥Type:A—Double—row connector
⑦Material:LP—LCP UL94V—0 ;
⑧Plating:XX—V01:Gold Plated ; SN:Tin Plated

X1254WS-2xXXA-LPXX	LCP	Phosphor	X1254H
PART NO	Material	Material(Pin)	Suitable XKE Housing

Recommended P.C.B Layout
General Tolerance ± 0.05

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: 1.25mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1254WVS-2xXXA-LPXX
APPROVED		SIZE: A4	DWG NO.:

PRECISION CO., LIMITED	SCALE	PAGE	REVISION
	N/A	1/1	A1