


为 您 的 产 品 保 驾 护 航

PRODUCT DATASHEET

Miniature Fuse

0473 Series, Time-Lag Fuse



Applications


0473 Series, Time-Lag Fuse is suitable for various kinds of electronic devices' circuit over current protection. Widely used in industrial of Lighting, Power supply and Adapter applications. etc.

Agency Approvals

Agency	File Number
	JDYX2.E486200

Dimensions and Structure

Unit:mm



Product Identification

No.	Part Name	Material
①	Body Encapsulated	Epoxy Coated
②	Lead wire	Tin plated Copper
③	Cap	Nickel Plated Brass
④	Fuse element	Ally wire
⑤	Body	Non-Transparent Ceramic Tube

Operating Characteristics

Ampere Rating	100%*In	200%*In	250%*In
0.062A~0.5A	4 hours Min	~	60 sec Max
0.63A~10A	4 hours Min	60 sec Max	~

Performance Specification

Amp Code	Ampere Rating(A)	Voltage Rating(V)	Breaking Capacity	I ² T Melting Integral (A ² s)
0473.100J	0.100	250/125	50A@125V/250VAC	0.01
0473.125J	0.125			0.02
0473.160J	0.160			0.04
0473.200J	0.200			0.06
0473.250J	0.250			0.09
0473.300J	0.300			0.12
0473.315J	0.315			0.15
0473.375J	0.375			0.19
0473.400J	0.400			0.31
0473.500J	0.500			0.46
0473.630J	0.630			0.78
0473.750J	0.750			0.93
0473.800J	0.800			1.10
0473001.J	1.00			1.30
04731.25J	1.25			2.60
047301.5J	1.50			3.10
047301.6J	1.60			3.90
0473002.J	2.00			7.20
047302.5J	2.50			12.0
0473003.J	3.00			15.0
04733.15J	3.15			19.0
047303.5J	3.50			24.0
0473004.J	4.00			29.0
0473005.J	5.00			59.0
047306.3J	6.30			90.0
0473007.J	7.00			145
0473008.J	8.00			190
0473010.J	10.0			220

Text	Result
Test Condition	All electrical test is to be conducted with the ambient air at a temperature of 25±5℃.
Load capacity	When the fuse loads through 100% of rated current, should blow within 4 hours.
Rising Temperature Test	When the 100% times of Ampere Rating passes the fuse, after reaching thermal balance ,the temperature on the fuse surface rising shall not be higher than 75℃. Note: Rising temperature = the Surface temperature - Ambient temperature.

Product Characteristics


Attribute	Data	
Lead Pull Strength	5N for 10±1 S	
Lead Thrust Strength	2N for 10±1 S	
Solder ability	Wave	260°C, ≤3S
	Soldering Iron	350±10°C, ≤3S
Soldering Heat Resistance	Wave	260°C, 10S
	Soldering Iron	350°C, 5S

Environmental Characteristic


Operating Temperature	Stock Condition
-55°C~+125°C	Humidity: Relative humidity ≤ 75% store 3 years in average

When choosing the fuse's specification, if the operating environmental temperature beyond the scope from 20~30°C, engineer should consider the environmental temperature's affection to fuses.

Please refer: Temperature Derating Curve:



Average Time-Current Curve



Installation Recommendations

Soldering	Temperature	Times
Wave	260°C Max(Solder Pot Temperature)	2-5S (Solder Dwell Time)
Hand-Solder	350±5°C(Solder Iron Temperature)	5S Max (Heating Time)

Packaging

Packaging Option	Quantity & Packaging Code	Quantity & Packaging Code	Quantity & Packaging Code
Bulk Packing	500 pcs/ bag	10 bags/ box	4 boxes/ carton
Taped Packing	-	3000 pcs/ box	4 boxes/ carton

Product Identification

0473 xxxx J

J=JDT Fuse

AMP Code

Refer to Amp Code column
of Electrical Characteristics
Table

Series

0473

Others

In the event that an impropriety is found beyond this specification, it shall be fixed by mutual agreement between the parties.