






技术指标:

- 1.温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压: 250V AC,DC.
- 3.耐电压: 800V AC/minute.
- 4.接触电阻: $\leq 20\text{m}\Omega$.
- 5.绝缘电阻: $\geq 1000\text{M}\Omega$.
- 6.额定电流: 3A AC,DC.

材料:

- 1.塑胶: PA66 白色

型号	CKT	A	B
BX-PHD2.0-2-2PJK	2*2	2.00	6.00
BX-PHD2.0-2-3PJK	2*3	4.00	8.00
BX-PHD2.0-2-4PJK	2*4	6.00	10.00
BX-PHD2.0-2-5PJK	2*5	8.00	12.00
BX-PHD2.0-2-6PJK	2*6	10.00	14.00
BX-PHD2.0-2-7PJK	2*7	12.00	16.00
BX-PHD2.0-2-8PJK	2*8	14.00	18.00
BX-PHD2.0-2-9PJK	2*9	16.00	20.00
BX-PHD2.0-2-10PJK	2*10	18.00	22.00
BX-PHD2.0-2-11PJK	2*11	20.00	24.00
BX-PHD2.0-2-12PJK	2*12	22.00	26.00
BX-PHD2.0-2-13PJK	2*13	24.00	28.00
BX-PHD2.0-2-14PJK	2*14	26.00	30.00
BX-PHD2.0-2-15PJK	2*15	28.00	32.00
BX-PHD2.0-2-16PJK	2*16	30.00	34.00
BX-PHD2.0-2-17PJK	2*17	32.00	36.00
BX-PHD2.0-2-18PJK	2*18	34.00	38.00
BX-PHD2.0-2-19PJK	2*19	36.00	40.00
BX-PHD2.0-2-20PJK	2*20	38.00	42.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PHD2.0-2-NPJK	版本 REV.	A		
			.X	±0.30									X.*	±5°
			.XX	±0.25									X.X*	±1°
			.XXX	±0.15										
					审核 CHECK	EVA			品名 TITLE	PHD2.0公头胶壳		页次 SHEET	1/1	
					核准 APPROVAL	JADE			客户料号 CUTM.NO.					
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)					