







	0.10	2*2P~2*5P
	0.13	2*6P~2*16P




SUGGESTED PCB LAYOUT
(COMPONENT SIDE)


技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$.
- 2.适用线规(Apply to gauge):AWG#28~#24
- 3.额定电压(Rated voltage):250V DC/AC(rms).
- 4.额定电流(Rated current):3.0A AC,DC.
- 5.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 6.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 7.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.

Part No	Pin	A	B
BX-PHD2.0-2-2PWT	2*2	2.00	6.00
BX-PHD2.0-2-3PWT	2*3	4.00	8.00
BX-PHD2.0-2-4PWT	2*4	6.00	10.00
BX-PHD2.0-2-5PWT	2*5	8.00	12.00
BX-PHD2.0-2-6PWT	2*6	10.00	14.00
BX-PHD2.0-2-7PWT	2*7	12.00	16.00
BX-PHD2.0-2-8PWT	2*8	14.00	18.00
BX-PHD2.0-2-9PWT	2*9	16.00	20.00
BX-PHD2.0-2-10PWT	2*10	18.00	22.00
BX-PHD2.0-2-11PWT	2*11	20.00	24.00
BX-PHD2.0-2-12PWT	2*12	22.00	26.00
BX-PHD2.0-2-13PWT	2*13	24.00	28.00
BX-PHD2.0-2-14PWT	2*14	26.00	30.00
BX-PHD2.0-2-15PWT	2*15	28.00	32.00
BX-PHD2.0-2-16PWT	2*16	30.00	34.00
BX-PHD2.0-2-18PWT	2*18	34.00	38.00
BX-PHD2.0-2-20PWT	2*20	38.00	42.00



2P 结构样式



序号	名称	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PHD2.0-2-NPWT	版本 REV.	A	
						.X	±0.25		X.*	±3°	审核 CHECK	EVA	品名 TITLE	2.0 Pitch D型双排卧贴	页次 SHEET	1/1
						.XX	±0.12		X.X*	±0.5°			客户料号 CUTM.NO.			
						.XXX	±0.05									
2	PHD卧贴(连绕)端子	铜合金/表面镀锡						核准 APPROVAL	JADE	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)		