








PIN ASSIGNMENT	
NAME	TYPE
P1	DAT2
P2	CD/DAT3
P3	CMD
P4	VDD
P5	DET
P6	CLK
P7	VSS
P8	DAT0
P9	DAT1
G1~G5	GND

NOTES:

1. MATERIAL:

1.1 Housing:High Temperature Thermoplastic
UL94V-0; Color Black.

1.2 Terminal:Copper Alloy.

1.3 Shell:Stainless Steel.

2. SPECIALITY:

2.1 Rated current:0.5A

2.2 Rated voltage:30V

2.3 Contact Resistance:50mΩ MAX

2.4 Insulation Resistance:100MΩ MIN 100V

DC

2.5 Dielectric withstanding voltage: 100V AC.

2.6 Solder ability:235±5℃, 5±0.5s.

2.7 Durability:5000 Cycles Min.

2.8 Operating condition:Temperature-40℃~
+85℃;

Humidity 80% R.H MAX

3. PLEASE CONTACT JITS SALES

REPRESENTATIVE TO VERIFY PRODUCT DETAILS &
AVAILABILITY

TABLE:

3	Housing	1PCS	LCP UL94V-0	BLACK
2	Shell	1PCS	SUS304-1/2H T=0.10	Ni30u"min Plat over all.Au 1u"plat on solder
1	Termiral	1SET	C5210R-EH T=0.12	Ni60u"min Plat over all.Au 1u"plat on solder and contact area Au 1u"min
N0	Description	Dosage	Material	Color/plating



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2° X.X' ±0.5°

UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

TF短体卡座中间P 1.7H

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW108-TF09-170B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2111240943

SHEET NO.

1 OF 1