

P-Channel Enhancement Mode MOSFET

1 Features

- $V_{DS} = -30V$, $I_D = -4.1A$
- $R_{DS(ON)} < 56m\Omega$ @ $V_{GS} = -10V$
- $R_{DS(ON)} < 84m\Omega$ @ $V_{GS} = -4.5V$
- High density cell design for extremely low $R_{DS(ON)}$
- Lead free product is acquired
- Conventional SOT-23 Package



2 Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Portable Instrumentation
- Load switch

3 Description

The SLMT330V4CPH provide the best combination of fast switching, low on-resistance and cost-effectiveness. The MOSFET is the P-Channel enhancement mode power field effect transistors with high cell density, trench technology. This high density process and design have been optimized switching performance and especially tailored to minimize on-state resistance.

4 Pin Configuration and Top View



SOT-23

5 Device Information

PART NUMBER	PACKAGE	BODY SIZE (NOM)
SLMT330V4CPH	SOT-23	2.90 mm x 2.40mm

6 Absolute maximum Ratings @25°C

RATING	SYMBOL	VALUE	UNITS
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	-4.1	A
Pulsed Drain Current	I_{DP}	-16	A
Total power dissipation	P_D	1.25	W
Channel temperature	T_J	-55 to +150	°C
Range of storage temperature	T_{STG}	-55 to +150	°C
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	100	°C/W

7 Electrical characteristics (@25°C unless otherwise specified)

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	I _D = -250μA, V _{GS} = 0V	-30			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250μA	-1.0		-3.0	V
Drain Cut Off Current	I _{DSS}	V _{DS} = -30V, V _{GS} = 0V			-1	μA
Gate Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} = 0V			±0.1	μA
Drain-Source ON Resistance	R _{DS(ON)}	V _{GS} = -10V, I _D = -4A		40	56	mΩ
		V _{GS} = -4.5V, I _D = -2A		60	84	mΩ
Dynamic Characteristics						
Total Gate Charge	Q _G	V _{DS} =-24V, I _D =-2A, V _{GS} = -10V		9		nC
Gate-Source Charge	Q _{GS}			1.5		nC
Gate-Drain Charge	Q _{GD}			2.3		nC
Input Capacitance	C _{ISS}	V _{DS} = -15V, V _{GS} = 0V, f = 1MHz		620		pF
Reverse Transfer Capacitance	C _{RSS}			76		pF
Output Capacitance	C _{OSS}			60		pF
Turn-On Delay Time	t _{d(on)}	V _{GS} =-10V, V _{DS} =-15V, I _D =-1A, R _G =3Ω		9		ns
Turn-Off Delay Time	t _{d(off)}			29		ns
Rise Time	t _r			3		ns
Fall Time	t _f			15		ns
Drain-Source Body Diode Characteristics						
Source-Drain Diode Forward Voltage	V _{SD}	I _S = -4.1A, V _{GS} = 0V		-0.8	-1.2	V

8 Typical Characteristics




Fig 1. Output Characteristics




Fig 2. Drain Current




Fig 3. Power Dissipation




Fig 4. Safe Operation Area(SOA)












Fig 5. Thermal Transient Impedance



9 Product dimension



10 PCB Layout Footprints (Units: mm)



11 Ordering Information

Part Number	Packaging	Reel Size
SLMT330V4CPH	3000/Tape & Reel	7 inch