








ABIDE BY ROHS

NO.	H	
01	2.5	
02	3.1	
03	3.4	
04	3.7	
05	...	
06	4.3	
07	4.5	
08	5.0	



P. C. B. Layout



CIRCUIT DIAGRAM

Remarks:

1. Rated current, Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $260 \pm 50\text{gf}$
5. Life requirements: 100000次
6. Withstand voltage: AC250V 1分钟
7. All materials comply with RoHS standards

5	Button	PPA	1	Red
4	Cover	SUS	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		$5 \leq X \leq 10$	± 0.15	产品型号 MODEL	6.2*6.2贴片
校准化 STANDARD		$X > 10$	± 0.25	产品编码 PART NO	ES625X-10XX-XXX-26-B
批准 APPROVALS		重量 WT.		视角 PROJ	
		产地 PRODUCTION		比例 SCALE	
				页码 SHEET	1 OF 1

ECN NO.	REV	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	---------------------	---------	--------	--------