






ROHS



PCB Layout Diagram
Top View

NOTE:

1.MATERIAL:

a.HOUSING:PPA

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Au-Plating)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 50 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN


c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C

3.PACKAGING:


a.PLASTIC TRAY(PLEASE REFER TO PAGE TWO FOR DETAILS)

b.TAPE OR REEL(PLEASE REFER TO PAGE THREE FOR DETAILS)



3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating		
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating		
1	HOUSING	1	PPA	BROWN		
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR		
COSTOMER DRAWING			 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	电池底座适用规格CR2032	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-SMT-B01-2AA	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
±3°			DWG.NO.		Projection	

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




Packaging information:

1. Each plate contains 10 rows, each row contains 10 PCS, for a total of 100 PCS;
2. 41 plastic trays are bundled together, with an empty plastic tray at the top, totaling 4000 products;
3. Each large plastic bag contains 40 plates of products, totaling 4000 products;
4. Each outer box contains a large plastic bag, totaling 4000 products
5. Seal the top and bottom of the outer box with adhesive tape to form the character "工";

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	电池底座适用规格CR2032	REV.	A
30-150	±0.35	ANGLE	PART NO. LAIL-CR2032-SMT-B01-2AA	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		DWG.NO.		Projection	

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



CUSTOMER DRAWING		 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
DRAWING		TITLE		电池底座适用规格CR2032	REV.	A	
CHECK							
APPROVAL							
TOLERANCES ARE		PART NO.	LAIL-CR2032-SMT-B01-2AA	UNITS	mm		
30-150	±0.35						ANGLE
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
		DWG.NO.		Projection			