


CONNECTORS

Operation: SMT& 1.0A 电流/电源连接器



ITEM NO.: DC-098-X165 (Series)

(L12.0×W8.4×H6.3 DC-POWER-SOCKETS)



Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	1.0A, 24V DC	
	Initial Contact Resistance	30mΩ max.	50mΩ max.
	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
	There No Load	6,000 Cycles	5,000 Cycles
Durable Performance	Rated Load	5,000 Cycles	4,000 Cycles
	Storage temp.	-25℃~+75℃(Operating Temp:)	

貼裝 SMT





側向導入 LATERAL

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Unit:mm




Operating Force

Inward

6.0N(100grams) $\pm$ 300gf

Exiting


6.5N(100grams) $\pm$ 300gf

Pin Definition



Material declaration

No.	NAME	MATERIAL	DESCRIPTION
① A	TERMINAL 接触端子	COPPER ALLOY 【G/F】	磷铜 C2680 t=0.3mm(Ag-Plated)
② B	TERMINAL 接触端子	COPPER ALLOY 【G/F】	磷铜 C2680 t=0.3mm(Ag-Plated)
③ C	TERMINAL 接触端子	COPPER ALLOY 【G/F】	磷铜 C2680 t=0.3mm(Ag-Plated)
④ D	TERMINAL 接触端子	COPPER ALLOY 【G/F】	磷铜 C2680 t=0.3mm(Ag-Plated)
⑤ E	SOUSHING 本体	BLACK	LCP 30%(Gray)耐热塑胶 UL94V-0



邀您使用(微信)小程序

硕方电子开关&连接器选型手册

手机扫码即可进入...



本品不屬於危害性廢棄物,須丟棄時可以委託
回收商予以回收再生處理。

Products do not belong to.

注記 NOTICE

- 碩方公司擁有最終解釋權; **The company reserves the right of final interpretation;**
- 文件禁止外洩、轉載; **Leaked and reproduced prohibited;**
- 未經授權修改無效。 **Modify is invalid.**

運送時本產品不要直接與水、酸鹼性化學物質接觸,或放置於含有以上氣體環境中,並且需要注意會有滑落、側翻的危險發生;運輸過程中不能有碰撞或者擠壓,須保證溫度與濕度適中[常溫 25℃,濕度在 50℃以內],不可導致材料變形或氧化。