



RoHS



CIRCUIT DIAGRAM

- NOTES:
TECHNICAL REQUIREMENTS:
1. OPERATING TEMPERATURE: -25~+85℃
2. CURRENT/VOLTAGE RATING:DC 12V 50mA
3. CONTACT RESISTANCE:≤50mΩ
4. INSULATION RESISTANCE:≥100MΩ
5. DIELECTRIC STRENGTH:AC250V
6. OPERATING FORCE: 160/260±50GF
7. LIFESPAN: 50000-70000CYCLES
8. TRAVEL DIMENSION OF THE SWITCH:0.25mm±0.1mm
9. DIMENSIONAL TOLERANCE:±0.15mm



TACT SWITCH SERIES			
H	D	H	D
4.30	3.50	14.50	3.00
4.50	3.45	15.00	3.00
5.00	3.40	15.50	3.00
5.50	3.30	16.00	3.00
6.00	3.20	16.50	3.00
6.50	3.00	17.00	3.00
7.00	3.00	17.50	3.00
7.50	3.20	18.00	3.00
8.00	3.00	18.50	3.00
8.50	3.00	19.00	3.00
9.00	3.00	19.50	3.00
9.50	3.00	20.00	3.00
10.00	3.00	21.00	3.00
10.50	3.00	22.00	3.00
11.00	3.00	23.00	3.00
11.50	3.00	24.00	3.00
12.00	3.00	25.00	3.00
12.50	3.00	26.00	3.00
13.00	3.00	27.00	3.00
13.50	3.00	28.00	3.00
14.00	3.00	29.00	3.00

TC-6601-H-XXX

H:4.3~29.0

160-160gf

260-260gf




PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:±0.05mm



5	CONTACT	4	BRASS	Ag PLATING	
4	HOUSING	1	PPA	BLC&K	
3	SPRING	1	SUS		
2	COVER	1	IRON/BRASS/SUS	Sn PLATING	
1	BUTTON	1	PPA	BLC&K	
NO	NAME	NUMBER	MATERIAL	ELECTRIC PLATING	REMARKS

TOLERANCE UNLESS OTHERWISE SPEC		ZHEJIANG FUGANG ELECTRONICS CO.,LTD				
BASIC DIMENSION	TOLERANCE	DSND	W Z Z	26.01.16	TITLE:SWITCH	
x.x	±0.30	CHKD	Y H C	26.01.16	PART NO:TC-6601-H-XXX	
x.xx	±0.20	APVD	L P J	26.01.16		
x.xxx	±0.10					
ANGLES	±3°			UNIT:mm	SCALE:1:1	SIZE:A4
					SHEET:1/1	

RoHS



卷装示意图仅供参考



NOTE:
1. THE CARTON IS MADE OF K=K MATERIAL.
2. THE OUTER SURFACE OF THE BOX IS CLEAN.
3. THIS BOX MUST PASS THE RELEVANT TESTING STANDARDS OF OUR COMPANY'S IQC.

包装数量										
开关高	W	P1	F	PCS/RELL	RELL/CARTON	SUM(PCS)				
4.3	16	12	7.5	1000	15	15000				
4.5										
5.0				700		10500				
5.5										
6.0										
6.5										
7.0										
7.5	24		11.5	500	11	5500				
8.0										
8.5										
9.0										
9.5										
10.0										
10.5										
11.0				400		4400				
11.5										
12.0				300		3300				
12.5										
13.0										
13.5										
14.0	16									
14.5										
15.0										
15.5										
16.0	280	3080								