


Features

- **Current transfer ratio**
(CTR: 80~600% at $I_F = 5\text{mA}$, $V_{CE} = 5\text{V}$)
- **High isolation voltage between input and output** (Viso = 3750V rms)
- **Collector - emitter breakdown voltage** $BV_{CEO} \geq 80\text{V}$
- **Operating Temperature:** $-55^\circ\text{C} \sim 110^\circ\text{C}$

HF



Applications

- Switching power supply, intelligent meter
- Industrial control, measuring instruments
- Office equipment such as copiers
- Household appliances: such as air conditioners, fans, water heaters, etc.

Mechanical Data

- **Case:** SSOP4
- **Molding Compound:** UL Flammability Classification Rating 94V-0
- **Terminals:** Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Ordering Information

TWS 3H7 (M) (G) (X) - (U) E
① ② ③ ④ ⑤ ⑥ ⑦

- ① Brand(TWS)
- ② Product series(3H7)
- ③ Package type(None:SSOP4)
- ④ Halogen option(None :Halogen free)
- ⑤ CTR Rank(A,B,C,D or None)
- ⑥ Lead frame (None: Copper)
- ⑦ Product Versions: E

Part Number	Package	Shipping Quantity	Marking Code
TWS3H7X*1-E	SSOP4	5000 pcs / Tape & Reel	TWS3H7X*1...E

Notes 1: X denotes CTR Rank : A, B, C, D None.

Marking Information

- "TWS" denotes brand
- "X" denotes CTR Rank : A, B, C, D , None.
- "Y" denotes Year : A(2024), B(2025), C(2026)
- "WW" denotes Week's number
- "N" denotes the day of Week.
- "E" fixed



Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Input	Forward Current	I _F	50	mA
	Peak Forward Current *1	I _{FM}	1	A
	Reverse Voltage	V _R	6	V
	Power Dissipation	P _D	70	mW
Output	Collector Power Dissipation	P _C	150	mW
	Collector Current	I _C	50	mA
	Collector-Emitter Voltage	V _{CEO}	80	V
	Emitter-Collector Voltage	V _{ECO}	7	V

Thermal Characteristics

Parameter	Symbol	Value	Unit
Total Power Dissipation	P_{TOT}	200	mW
Isolation Voltage ^{*2}	V_{ISO}	3750	Vrms
Rated Impulse Isolation Voltage	V_{IOTM}	5000	V
Rated Repetitive Peak Isolation Voltage	V_{IORM}	600	V
Thermal Resistance Junction-to-Air	$R_{\theta JA}$	430	°C/W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	350	°C/W
Thermal Resistance Junction-to-Lead	$R_{\theta JL}$	368	°C/W
Operating Temperature	T_{OPR}	-55 ~ +110	°C
Storage Temperature Range	T_{STG}	-55 ~ +125	°C
Soldering Temperature ^{*3}	T_{SOL}	260	°C

Notes:

1. Pulse width $\leq 1\mu s$, Duty ratio: 0.001
2. 40 to 60% RH, AC for 1 minute
3. For 10 seconds

Electrical Characteristics (@ $T_A = 25^\circ C$ unless otherwise specified)

Parameter		Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	V_F	$I_F = 20mA$	-	1.2	1.4	V
	Peak Forward Voltage	V_{FM}	$I_{FM} = 0.5A$	-	-	3.0	V
	Reverse Current	I_R	$V_R = 4V$	-	-	10	μA
	Input Capacitance	C_{in}	$V_R = 0V, f = 1kHz$	-	30	250	pF
Output	Collector-Emitter Dark Current	I_{CEO}	$V_{CE} = 20V, I_F = 0$	-	-	100	nA
	Collector-Emitter Breakdown Voltage	BV_{CEO}	$I_C = 0.1mA, I_F = 0$	80	-	-	V
	Emitter-Collector Breakdown Voltage	BV_{ECO}	$I_E = 10\mu A, I_F = 0$	7	-	-	V
Transfer Characteristics	Collector Current	I_C	$I_F = 5mA, V_{CE} = 5V$	2.5	-	30	mA
	Current Transfer Ratio	CTR	$I_F = 5mA, V_{CE} = 5V$	80	-	600	%
	Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_F = 20mA, I_C = 1mA$	-	0.1	0.2	V
	Isolation Resistance	R_{ISO}	$V_{IO} = 500Vdc$ 40~60% R.H.	1×10^{12}	-	-	Ω
	Isolation current	R_{isc}	DC6000V, 40~60% R.H.	-	-	2	μA
	Floating Capacitance	C_{IO}	$V_{IO} = 0, f = 1MHz$	-	0.6	1.0	pF

	Cut-off frequency	f_c	$V_{CE} = 5V, I_C = 2mA$ $R_L = 100\Omega, -3dB$	-	80	-	kHz
	Turn On Time	T_{on}	$V_{CE} = 2V, R_L = 100\Omega$	-	4	18	μs
	Turn Off Time	T_{off}	$I_C = 2mA$	-	3	18	

Rank Table of Current Transfer Ratio CTR

Rank Mark	Min. (%)	Max. (%)	Condition
A	80	160	$I_F = 5mA, V_{CE} = 5V$
B	130	260	
C	200	400	
D	300	600	
No mark	80	600	

Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Fig.1 Allowable Forward Current vs. Ambient Temperature




Fig.2 Allowable collector power dissipation vs. Ambient Temperature ($^\circ\text{C}$)




Fig.3 Relative Current Transfer Ratio vs. Forward Current




Fig.4 Forward Current vs. Forward Voltage




Fig.5 Collector Current vs. Collector-emitter Voltage




Fig.6 Relative Current Transfer Ratio vs. Ambient Temperature




Fig.7 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig.8 Collector Dark Current vs. Ambient Temperature




Fig.9 Response Time vs. Load Resistance




Fig.10 Frequency Response




Fig.11 Collector-emitter Saturation Voltage vs. Forward Current






Fig.12 Switching Time Test Circuit & Waveforms




Package Outline Dimensions (unit: mm)


SSOP4



SOLDERING FOOTPRINT (unit: mm)



Reflow soldering




	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	°C
Preheat time	ts	60	120	s
Ramp-up rate(T_L to T_P)			3	°C/s
Liquidus temperature	T_L		217	°C
Time above T_L	t_L	60	150	s
Peak temperature	T_P		260	°C
Time during which T_c is between (T_P-5) and T_P	t_P		30	s
Ramp-down rate(T_P to T_L)			6	°C/s

Note:

Reflow soldering is recommended at the temperatures and times shown, no more than three times.

Wave soldering



Profile feature	
Average ramp-up rate	~200°C/s
Heating rate during preheat	1°C/s to 2°C/s typical; 4°C/s maximum
Final preheat temperature Ts	~130°C
Preheat time (25°C to Ts)	> 60s
Peak temperature T_P	260°C
Time within peak temperature t_P	10s
Ramp-down rate	5°C/s maximum

Soldering with hand soldering iron

- Hand soldering iron is only used for product rework or sample testing.
- Hand soldering iron requirements: Temperature: 360 °C±5°C within 3s.

Packing

Package Type	Packing Form	Quantity per Tube & Reel	Quantity per Box	Quantity per Carton	Antistatic Bag Specification	Box Specification	Carton Specification	Note
SSOP4	Reel($\phi 330$ mm)	5000 pcs/reel	3 reels /box	5 boxes /ctn	380*420mm	350*340*60mm	365*330*370mm	Leave 50 Spaces at the beginning and 100 Spaces at the end


■Summary table

■SSOP4 (Reel)

Qty/reel: 5000 pcs. Qty/box: 15000 pcs.

Qty/ctn : 75000 pcs.

Schematic: (unit:mm)



IMPORTANT NOTICE

TAIWEI semiconductor the right to make changes without further notice to any product herein to make corrections, modifications , improvements , or other changes. TAIWEI semiconductor does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others .