





REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	10/09/2021	PECK




P.C.B LAYOUT
TOP VIEW

PIN	φ 1.65	φ 2.0	φ 2.5
APPO			

主要技术性能		公差
额定电负荷	DC 30V\0.5A	X.±0.20
接触电阻	≤0.03Ω	.X±0.10
绝缘电阻	≥100MΩ	.XX±0.05
耐压	AC500V (50Hz)/min	.XXX±0.02
插拔力	3-20N	X°.±5°
使用温度范围	-30~70℃	.X°±2°
使用寿命	5000次	.XX°±1°

7						
6	DC-022	中心针	1	H62黄铜棒		铜锡
5	DC-022	平片	1	H62黄铜带	T=0.30	铜锡
4	DC-022	黄板	1	酚醛板	T=1.20	
3	DC-022	弹片	1	锰钢带	T=0.25	锡梯
2	DC-022	插片	1	H62黄铜带	T=0.30	铜锡
1	DC-022	底座	1	PA	黑色	
序号	产品编号	产品名称	数量	材料	规格	电镀



DIMENSION CLASSIFICATION			台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
■ : CRITICAL										
☒ : MAJOR										
TOLERANCE TABLE			TITLE		DC-022-T20 直立式帶螺紋電源插座			開關, 連接器 SOFNG		
.X	±	0.40	PART NO.					SERIES	SD106	
.XX	±	0.25	APPROVED	Peck	DWG NO.		DC-022-T20			
.XXX	±	0.10	CHECKED	Paul	SCALE	1:1	UNIT	mm	SIZE	A4
ANGLE	±	2°	DRAWIN	David			REV	AO	SHEET NO.	1/1