








PCB Layout(Pattern side)

NO.1	
PART NO	H
A	4.3
B	4.5

NO.2	
PART NO	vigor
2	130±30
3	180±30
4	250±30

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER



Circuit Diagram

NOTE:
Rating: DC 12V 50mA
Operating force: 260±50gf
Insulation resistance: $\geq 100M\Omega$
Contact resistance: $\leq 100m\Omega$ Max
IP Rating: IP67

⑥	Internal button	—	1	LCP	Black	—
⑤	Terminal	—	4	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	SUS	—	—
①	Keystoke	—	1	Silica gel	Red	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2023.10.27					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1102SG-□□□□-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
		±2'	DRAWING NO.	_____		SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.