




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

DESCRIBE:THERE ARE TWO PACKAGING OPTIONS FOR THIS PRODUCT.
1.PE BAG PACKAGING
2.TAPE OR REEL




PCB Layout Diagram
Top View

1	TERMINAL(+)	1	C5191 T=0.25mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司	
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD	
CHECK				
APPROVAL				
TOLERANCES ARE			TITLE	电池扣CR2032
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-M0-01
10-30	±0.2		UNITS	mm
5-10	±0.15		DWG.NO.	
0-5	±0.1		Projection	

ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- Packaging information:
1. Each bag contains 500 products, with relevant labels attached to the outside of the bag;
 2. Place a small cardboard box every 6 bags;
 3. Each small cardboard box contains 6 bags of products, totaling 3000 products;
 4. Each outer box contains 4 small paper boxes, totaling 12000 products
 5. Seal the top and bottom of the outer box with adhesive tape to form the character "工";





COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	电池扣CR2032	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-MO-01	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.		Projection	

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



Packaging information:

1. Each roll contains 500 products, with relevant labels attached to the outside of the roll;
2. Put every 6 rolls in a plastic bag;
3. Each outer box contains 6 plates, with a total of 3000 products;
4. Seal the top and bottom of the outer box with adhesive tape to form the character "工";
5. Battery buckle packaging material CR2032-P28 SMT roll pack(MY-2032-P28-01-R).



Detail A

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	电池扣CR2032	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-M0-01	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
±3°			DWG.NO.		Projection	