









RoHS

版本 REV A0	变更事项 CHANGE CONTENT	依据 THEREUNDER	变更日期 DATE
-----------------	------------------------	------------------	--------------



SECTION A-A



技术参数 SPECIFICATIONS

线数 (Poles) : 2~16

适用线规 (Applicable wires) : AWG28#~22#

适用基板厚度 (Applicable PC board thickness) : 1.6mm

温度范围 (Temperature range) : -25℃~85℃

额定电压 (Voltage rating) : 250V.Ac/Dc

额定电流 (Current rating) : 2A

接触电阻 (Contact resistance) : ≤0.02Ω

绝缘电阻 (Insulation resistance) : ≥1000MΩ

耐压 (Withstand voltage) : 1000V.Ac/1min

线数 Poles	型号 Type	尺寸Dimensions mm	
		A	B
2	PH-2A	2.00	6.00
3	PH-3A	4.00	8.00
4	PH-4A	6.00	10.00
5	PH-5A	8.00	12.00
6	PH-6A	10.00	14.00
7	PH-7A	12.00	16.00
8	PH-8A	14.00	18.00
9	PH-9A	16.00	20.00
10	PH-10A	18.00	22.00
11	PH-11A	20.00	24.00
12	PH-12A	22.00	26.00
13	PH-13A	24.00	28.00
14	PH-14A	26.00	30.00
15	PH-15A	28.00	32.00
16	PH-16A	30.00	34.00

	单位 UNIT	mm	深圳市泰华电子有限公司 TaiHua Electronics Co., Ltd		
	比例 SCALE				
x. ±0.5	x. °±	核准: 吕灿东	版本: A0	产品名称 Production name	PH-2A~16A-L3.3(直针)
. x ±0.30	. x °±	APPROVED BY	审核: 徐章雄	产品料号 Product No	TH52003611610
. xx ±0.20	. xx °±	CHECKED BY	制图: 封文辉	客户料号 Client No	
. xxx ±0.05	. xxx °±	DRAWN BY	日期:		

2	针	黄铜镀锡		
1	基座	PA66 UL94V-(0)		
序号	名称	材料	数量	备注