

RoHS

REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

liuhongping

2023.01.02

YELLOW LED

GREEN LED

⑪ 15.90±0.35

⑪ 21.60±0.35

⑫ 13.55±0.35

⑬ 3.20±0.38

⑫ 0.44±0.10

⑬ 11.43

⑭ 15.70±0.30

⑮ 2.50±0.10

⑯ 2.54±0.38

⑰ 4.57±0.38

⑱ 1.20±0.10

⑲ 3.05±0.38

⑳ 6.35±0.38

㉑ 8.89±0.38

㉒ 13.45


㉓ 3.28

㉔ 1.27

㉕ 3.18

㉖ 2.54

㉗ 7.62



NOTES:

1. MATERIAL:

1.1 HOUSING: PBT UL94V-0; COLOR: BLACK

1.2 INSERT: PBT UL94V-0 BLACK.

1.3 TERMINAL: PHOSPHOR BRONZE (C5191)

1.4 SHELL: C2680

2. FINISH:

2.1 TERMINAL: 6u" PLATED ON CONTACT AREA;

Tin 50u" MIN. PLATED ON SOLDER AREA;

Ni 20u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 20u" MIN. PLATED OVERALL

3. ELECTRICAL SPECIFICATION @25°C:

3.1 INDUCTANCE: 350UH MIN WITH 8MA DC BIAS.

3.2 INSERTION LOSS :

1-100MHZ -1DB MAX.

3.3 RETURN LOSS :

1-30MHZ -18DB MIN.

30-60MHZ -16DB MIN.

60-80MHZ -12DB MIN.

3.4 COMMON MODE REJECTION: 1-100MHZ -30DB MIN.

3.5 CROSS TALK: 1-100MHZ -30DB MIN.

4. OPERATING AND STORAGE TEMPERATURE:

4.1 OPERATING TEMPERATURE : -40°C TO +85°C.

4.2 STORAGE TEMPERATURE : -40°C TO +85°C.

5. ELECTRICAL SPECIFICATION:

5.1 RATED CURRENT: 1.5A

5.2 CONTACT RESISTANCE: 40m Ω MAX(INITIAL). 50m Ω MAX (AFTER).

5.3 INSULATION RESISTANCE: 500MΩ MIN.

5.4 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.

6. MACHINERY SPECIFICATION:

6.1 MATING FORCE: 22.4N MAX.

UNMATING FORCE: 22.4N MAX.

6.2 DURABILITY: 750 CYCLES MIN.

7. SALT SPRAY: 24H (contact area)

8. WAVE SOLDERING: SOLDER TEMPERATURE 235 ~ 260℃


MILLIMETERS	INCH
X.* ±2"	X.* ±2"
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBilal Metal Plastic Technology Co.,Ltd	
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBilal Metal Plastic Technology Co.,Ltd	

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD


TITLE	RJ45 1x1 全屏蔽 无弹带灯 10/100 BASE			DR	
PART NO.	109435471			CHKD	
PRO J.	PAGE	1/3	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.	

RoHS

PCB CONNECTIONS







RJ45 CONNECTIONS



Emitting Color	$\lambda_p(\text{nm})$	$V_f@I_f=20\text{mA}$
Green	565	1.8-2.5V
YELLOW	585	1.8-2.5V

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X." ±2"	X." ±2"				
X ±0.30	.X ±0.012	TITLE RJ45 1x1 全屏蔽 无弹带灯 10/100 BASE		DR	
XX ±0.20	.XX ±0.008	PART NO. 109435471		CHKD	
XXX ±0.10	.XXX ±0.004	PRO J. PAGE 2/3 UNITS mm		APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			SIZE A4	SCALE 1:1	DIS NO.

RoHS



作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。最后一排产品端子朝内摆放 每盘吸塑盒内放120PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合，一箱装 10盘
4. 外箱用胶布工字型封箱，并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装，少装，方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

120	10	1200PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X." ±2"	X." ±2"				
X ±0.30	.X ±0.012	TITLE	RJ45 1x1 全屏蔽 无弹带灯 10/100 BASE	DR	
XX ±0.20	.XX ±0.008	PART NO.	109435471	CHKD	
XXX ±0.10	.XXX ±0.004	PRO J.	PAGE 3/3 UNITS mm	APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			SIZE A4	SCALE 1:1	DIS NO.