

RoHS

REV.

ECN.#

DESCRIPTION

NAME





DATE

A0

NEW RELEASE

liuhongping

2023.01.02



## NOTES:

## 1. MATERIAL:

1.1 HOUSING: PBT UL94V-0; COLOR: BLACK

1.2 TERMINAL: C51000

1.3 SHELL: C2680

## 2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;  
G/F PLATED ON SOLDER AREA;  
Ni 20u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 20u" MIN. PLATED ON SOLDER AREA;

## 3. ELECTRICAL SPECIFICATION:

3.1 RATED CURRENT: 1.5A

3.3 CONTACT RESISTANCE: 40m Ω MAX(INITIAL). 50m Ω MAX (AFTER).

3.4 INSULATION RESISTANCE: 500MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.

## 4. MACHINERY SPECIFICATION:

4.1 MATING FORCE: 22.4N MAX.

UNMATING FORCE: 22.4N MAX.

4.2 DURABILITY: 750 CYCLES MIN.

## 5. ENVIRONMENTAL SPECIFICATION :

5.1 OPERATING CONDITION: TEMPERATURE -40°C~+60°C;  
HUMIDITY 80% R.H MAX

5.2 SALT SPRAY: 8H

## 6. SOLDER ABILITY: 245±5°C, 5±0.5s

## 7. WAVE SOLDERING: SOLDER TEMPERATURE 235 ~ 260℃





|      |     |
|------|-----|
| 8    | —   |
| 7    | —   |
| 6    | RX- |
| 5    | —   |
| 4    | —   |
| 3    | RX+ |
| 2    | TX- |
| 1    | TX+ |
| PIN序 | 说明  |

| MILLIMETERS                                                                                                                                                                                                                      | INCH        |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| X* ±2*                                                                                                                                                                                                                           | X* ±2*      |
| X ±0.30                                                                                                                                                                                                                          | .X ±0.012   |
| XX ±0.20                                                                                                                                                                                                                         | .XX ±0.008  |
| XXX ±0.10                                                                                                                                                                                                                        | .XXX ±0.004 |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd<br>COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd |             |

东莞市金比莱五金塑胶科技有限公司  
DONGGUAN JBL TECH CO., LTD

|          |                        |           |         |
|----------|------------------------|-----------|---------|
| TITLE    | RJ45 8P8C DIP 90° 无弹无灯 | DR        |         |
| PART NO. | 109530141              | CHKD      |         |
| PRO J.   | PAGE 1/2               | UNITS mm  | APPD    |
| SIZE     | A4                     | SCALE 1:1 | DIS NO. |

RoHS



#### 作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示, 每盘吸塑盒内放100PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合, 一箱装 20盘
4. 外箱用胶布工字型封箱, 并在外箱贴上相应标签

#### 注 意 事 项

1. 吸塑盒内产品不可多装, 少装, 方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

|              |                 |          |                 |               |
|--------------|-----------------|----------|-----------------|---------------|
| 100          | 20              | 2000PCS  | --KG            | --KG          |
| PCS/<br>TRAY | TRAY/<br>CARTON | QUANTITY | GROSS<br>WEIGHT | NET<br>WEIGHT |

|                                                                                                                                                                                                                                              |             |          |            |                                                                                                                                                                    |  |                        |       |       |         |      |  |  |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|----------|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------|-------|-------|---------|------|--|--|--|
| MILLIMETERS                                                                                                                                                                                                                                  |             | INCH     |            | <div></div> <div>东莞市金比莱五金塑胶科技有限公司</div> <div>DONGGUAN JBL TECH CO., LTD</div> |  |                        |       |       |         |      |  |  |  |
| X." ±2"                                                                                                                                                                                                                                      | X." ±2"     | .X       | .X         |                                                                                                                                                                    |  |                        |       |       |         |      |  |  |  |
| X ±0.30                                                                                                                                                                                                                                      | .X ±0.012   | XX ±0.20 | .XX ±0.008 |                                                                                                                                                                    |  |                        |       |       |         |      |  |  |  |
| XXX ±0.10                                                                                                                                                                                                                                    | .XXX ±0.004 |          |            |                                                                                                                                                                    |  |                        |       |       |         |      |  |  |  |
| THESE DRAWINGS AND SPECIFICATIONS ARE<br>THE PROPERTY OF DongGuan JinBiLai<br>Metal Plastic Technology Co.,Ltd<br>COPIED OR USED IN ANY MANNER WITHOUT THE<br>PRIOR WRITTEN CONSENT OF DongGuan<br>JinBiLai Metal Plastic Technology Co.,Ltd |             |          |            | TITLE                                                                                                                                                              |  | RJ45 8P8C DIP 90° 无弹无灯 |       | DR    |         |      |  |  |  |
|                                                                                                                                                                                                                                              |             |          |            | PART NO.                                                                                                                                                           |  | 109530141              |       |       |         | CHKD |  |  |  |
|                                                                                                                                                                                                                                              |             |          |            | PRO J.                                                                                                                                                             |  | PAGE                   | 2/2   | UNITS | mm      | APPD |  |  |  |
| <div></div>                                                                                                                                             |             |          |            | SIZE                                                                                                                                                               |  | A4                     | SCALE | 1:1   | DIS NO. |      |  |  |  |
|                                                                                                                                                                                                                                              |             |          |            |                                                                                                                                                                    |  |                        |       |       |         |      |  |  |  |