

RoHS

REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

liuhongping

2023.01.02

A1

修改结构, 配合自动机生产

liuhongping

2026.02.02

① 63.75±0.38

② 15.75x3=47.25±0.30

YELLOW
LEFTGREEN
RIGHT

③ 13.1

④ 15.75

⑥ 2.60

⑤ 59.95±0.3

⑦ 15.7±0.38

⑪ 2.70±0.38

⑫ 3.56±0.38

⑧ 1.7

⑨ 1.40±0.10

⑩ 3.43

NOTES:

1. MATERIAL:

1.1 HOUSING: PA46 UL94V-0; COLOR: BLACK

1.2 TERMINAL: C51000 Ø0.46mm

1.3 SHELL: SUS304

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;
G/F PLATED ON SOLDER AREA;
Ni 20u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 20u" MIN. PLATED OVERALL

2.3 LED: Tin 50u" MIN. PLATED OVERALL.

3. ELECTRICAL SPECIFICATION:

3.1 LOAD RATING: 125VAC,1.5A;

3.3 CONTACT RESISTANCE: 40mΩ MAX(INITIAL).
50mΩ MAX (AFTER).

3.4 INSULATION RESISTANCE: 500MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.

4. MACHINERY SPECIFICATION:

4.1 DURABILITY: 750 CYCLES MIN.


5. ENVIRONMENTAL SPECIFICATION:

5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;
HUMIDITY 80% R.H MAX

5.2 SALT SPRAY: 8H

6. SOLDER ABILITY: 245±5°C, 5±0.5s

7. WAVE SOLDERING: SOLDER TEMPERATURE 235°C~260°C



PCB Layout





黄LED	9	10
绿LED	11	12

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	

东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 1x4 8P8C 全屏蔽 无弹片 黄绿LED			DR	
PART NO.	109315281			CHKD	
PRO J.	PAGE	1/2	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.	

RoHS



作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。最后一排产品端子朝内摆放 每盘吸塑盒内放20PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合，一箱装 50盘
4. 外箱用胶布工字型封箱，并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装，少装，方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；



20	50	1000PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X." ±2"	X." ±2"				
X ±0.30	.X ±0.012	TITLE		DR	
XX ±0.20	.XX ±0.008	PART NO.		CHKD	
XXX ±0.10	.XXX ±0.004	PRO J.		APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		PAGE	2/2	UNITS	mm
		SIZE	A4	SCALE	1:1
		DIS NO.			