

RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		NEW RELEASE	07/12'21	JX	/	MOON

SPECIFICATIONS:

- ELECTRICAL CHARACTERISTICS
 - CURRENT RATING: 0.5 AMP
 - VOLTAGE RATING: 40 V
 - CONTACT RESISTANCE: 30MILLIOHMS MAX
 - INSULATION RESISTANCE: 100M MIN. @500V DC
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE
- MECHANICAL CHARACTERISTICS:
 - INSERTION FORCE : 4.5KGF MAX.
 - WITHDRAWING FORCE : 1KGF ~ 4KGF.
- LIFE TEST: 10000 CYCLES
- OPERATING TEMPERATURE: -25° C TO +85° C

PART No. :

105010792

HDMI SERIES

PLATING:

01:G/F+MATTE TIN

PAKING:

2: REEL

SERIAL NO.

SHELL	1	C2680R-H Ni T=0.5MM, 50u"MIN. NICEL ALL OVER
TERMINAL	19	C2680R-H G/F;MATTE TIN
HOUSING	1	LCP E130i UL94V-0 BLACK
PART NAME	QTY	MATERIAL PLATING & COLOR

MILLIMETERS	INCH	UNITS	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd							
X° ± 2°	X° ± 2°	MM		PART NUMBER: 105010792-A			TITLE: HDMI正向沉板铜壳镀窗口斜口两K脚两直脚(外壳点焊)			
.X ±0.38	.XX ±0.015	MAT'L								
SEE NOTES										
.XX ±0.25	.XXX ±0.010	FINISH		APPD: 105010792-A			DWG NO. : C-105010792-A-00			
.XXX ± 0.15	.XXXX ±0.006	SEE NOTES								
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		QTY	CHKD:				SCALE	SHEET	REV.	
		SEE NOTES	DR:							

E

MILLIMETERS	INCH	UNITS	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd						
$X^{\circ} \pm 2^{\circ}$	$X^{\circ} \pm 2^{\circ}$	MAT'L	PART NUMBER: 105010792-A			TITLE: HDMI 正向沉板铜壳镀镍窗口斜口两X脚两直脚 (外壳点焊)			
$.X \pm 0.38$	$.XX \pm 0.015$	SEE NOTES							
$.XX \pm 0.25$	$.XXX \pm 0.010$	FINISH	APPD:			DWG NO. : C-105010792-A-00			
$.XXX \pm 0.15$	$.XXXX \pm 0.006$	SEE NOTES							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		QTY	CHKD:						
		SEE NOTES	DR:						
						1:1	2/2	A0	