


Description

The WTM40N20VMP/VP/VF uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge. It can be used in a wide variety of applications.




General Features

- V_{DS} 200V
- I_D (at $V_{GS} = 10V$) 40A
- $R_{DS(ON)}$ (at $V_{GS} = 10V$) < 45mΩ
- 100% Avalanche Tested
- RoHS Compliant

Application

- Power switch
- DC/DC converters



Schematic diagram

Device	Package	Packaging	Package	Packaging
WTM40N20VMP/VP/VF	TO-220 TO-220F	50pcs/Tube	TO-247	30pcs/Tube

Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	200	V
Continuous Drain Current	I_D	40	A
Pulsed Drain Current (note1)	I_{DM}	160	A
Gate-Source Voltage	V_{GS}	± 20	V
Single pulse avalanche energy (note3)	E_{AS}	400	mJ
Power Dissipation	P_D	220	W
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 To 150	$^\circ\text{C}$

Thermal Resistance

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	0.68	$^\circ\text{C/W}$



Specifications $T_J = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Parameters						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	200	--	--	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 200V, V_{GS} = 0V$	--	--	1	μA
Gate-Source Leakage	I_{GSS}	$V_{GS} = \pm 20V$	--	--	± 100	nA
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	2.5	3.0	3.5	V
Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 20A$	--	36	48	m Ω
Forward Transconductance	g_{FS}	$V_{DS}=25V, I_D=20A$	25	--	--	S
Dynamic Parameters						
Input Capacitance	C_{iss}	$V_{GS} = 0V,$ $V_{DS} = 25V,$ $f = 1.0MHz$	--	6500	--	pF
Output Capacitance	C_{oss}		--	290	--	
Reverse Transfer Capacitance	C_{rss}		--	220	--	
Total Gate Charge	Q_g	$V_{DD} = 30V,$ $I_D = 30A,$ $V_{GS} = 10V$	--	163	--	nC
Gate-Source Charge	Q_{gs}		--	31	--	
Gate-Drain Charge	Q_{gd}		--	64	--	
Turn-on Delay Time	$t_{d(on)}$	$V_{DD} = 30V,$ $I_D = 2A,$ $R_G = 2.5\Omega$	--	26	--	ns
Turn-on Rise Time	t_r		--	24	--	
Turn-off Delay Time	$t_{d(off)}$		--	91	--	
Turn-off Fall Time	t_f		--	39	--	
Drain-Source Body Diode Characteristics						
Continuous Body Diode Current	I_S	$T_C = 25^{\circ}C$	--	--	40	A
Body Diode Voltage	V_{SD}	$T_J = 25^{\circ}C, I_{SD} = 20A, V_{GS} = 0V$	--	--	1.2	V
Reverse Recovery Time	T_{rr}	$I_S = 20A, V_{GS} = 0V$ $di/dt=100A/us$	--	42	--	ns
Reverse Recovery Charge	Q_{rr}		--	66	--	nc



Notes

1. Repetitive Rating: Pulse width limited by maximum junction temperature
2. Identical low side and high side switch with identical R_G
3. EAS condition : $T_J=25^\circ\text{C}$, $V_{DD}=50V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$.



Gate Charge Test Circuit



Switch Time Test Circuit



EAS Test Circuit



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Gate Charge




Figure 4. Drain Source On Resistance




Figure 5. Capacitance





Figure 6. Source-Drain Diode Forward



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Drain-Source On-Resistance




Figure 8. Safe Operation Area






Figure 9. Normalized Maximum Transient Thermal Impedance




TO-220 Package Information




Symbol	Dimensions in Millimeters		
	MIN.	NOM.	MAX.
A	4.37	4.57	4.7
A1	1.25	1.3	1.4
A2	2.2	2.4	2.6
b	0.7	0.8	0.95
b2	1.17	1.27	1.47
c	0.45	0.5	0.6
D	15.1	15.6	16.1
D1	8.8	9.1	9.4
D2	5.5		
E	9.7	10	10.3
e	2.54BSC		
e1	5.08BSC		
H1	6.25	6.5	6.85
L	12.75	13.5	13.8
L1		3.1	3.4
ØP	3.4	3.6	3.8
Q	2.6	2.8	3

TO-220F Package Information




Symbol	Dimensions In Millimeters	
	Min	Max
A	4.3	4.75
A1	0.7 REF	
A2	2.3	2.85
A3	2.5	2.9
b	0.38	0.42
b1	1.22	1.28
C	1.08	1.2
c	0.48	0.52
D	10.15	10.45
E	15.7	15.95
e	2.574 TYP	
F	3.470 REF	
h	0	0.8
L	28.78	28.9
L1	2.99	3.1

TO-247 Package Information



SYMBOL	MILLIMETERS		
	MIN	Nominal	MAX
A	4.80	5.00	5.20
A1	2.41 REF		
b	1.00	1.20	1.40
c	0.40	0.60	0.80
D	15.60	15.80	16.00
e	5.45 REF		
H	6.15 REF		
L	19.35	19.95	20.55
L1	20.80	21.00	21.20
Ø	3.20	3.50	3.80

Marking Information



WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.