




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	20JUN25	F.Z	R.B





- NOTES
- 1 MATERIAL:
HOUSING:GLASS FILLED THERMO PLASTIC
POLYESTER(UL94-V0),COLOR:ORANGE
CONTACT:COPPER ALLOY
RETENTION LEG:COPPER ALLOY
FINISH(ALL OVER):TIN PLATING:2.0um MIN OVER
NICKEL PLATING WITH 1.27um MIN;
 - 2 3.RATED OPERATION VOLTAGE:1000V DC(POLLUTION DEGREE:2);
4.OPERATION TEMPERATURE:-40°C - +125°C;
5.PACKAGING IN TAPE AND REEL;
6.VACUUM GRIP AREA FREE OF BURR AND EJECTOR PIN MARK, DIAMETER $\phi 9.0$;
7.THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".


8	Y	7	24.5	34.4	39.4	40.58	2-2464043-8
	X	7	24.5	34.4	39.4	40.58	1-2464043-8
6	Y	5	17.5	27.4	32.4	33.58	2-2464043-6
	X	5	17.5	27.4	32.4	33.58	1-2464043-6
5	Y	4	14.0	23.9	28.9	30.08	2-2464043-5
	X	4	14.0	23.9	28.9	30.08	1-2464043-5
4	Y	3	10.5	20.4	25.4	26.58	2-2464043-4
	X	3	10.5	20.4	25.4	26.58	1-2464043-4
POS	KEY	n	A	B	C	D	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	20JUN2025	 TE Connectivity			
		CHK	20JUN2025				
		APVD	20JUN2025				
		PRODUCT SPEC					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DYNAMIC HV10 HDR, 1-ROW H-TYPE, ASSY, 4-8POS TIN PLATING			
		0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES $\pm 0.5^\circ$		APPLICATION SPEC 108-161098			
MATERIAL		FINISH		SIZE A3			
				CAGE CODE 00779			
				DRAWING NO C= 2464043			
				RESTRICTED TO -			
				SCALE 2:1			
				SHEET 1 OF 3			
				REV A			
				CUSTOMER DRAWING			




© 2025 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Fisher ZHU 20JUN2025	 TE Connectivity				
		CHK Rick.BIAN 20JUN2025					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Rick.BIAN 20JUN2025	NAME DYNAMI HV10 HDR, 1-ROW H-TYPE, ASSY, 4-8POS TIN PLATING				
		PRODUCT SPEC 108-161098					
	0 PLC ± 0.3	APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	1 PLC ± 0.3		A3	00779	C= 2464043		
	2 PLC ± 0.3						
	3 PLC ± 0.3	WEIGHT					
	4 PLC ± 0.3						
	ANGLES ± 0.5 °						
MATERIAL	FINISH						
CUSTOMER DRAWING			SCALE	SHEET		REV	
			3:1	2 OF 3		A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD



P/N: 2-2464043-8
(8POS: Y-KEY)



P/N: 2-2464043-6
(6POS: Y-KEY)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Fisher.ZHU 20JUN2025	 TE Connectivity				
		CHK Rick.BIAN 20JUN2025					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Rick.BIAN 20JUN2025	NAME &DWG_TITLE &DWG_TITLE_2 TIN PLATING				
	0 PLC ±0.3	PRODUCT SPEC					
	1 PLC ±0.3	108-161098					
	2 PLC ±0.3	APPLICATION SPEC					
	3 PLC ±0.3	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	4 PLC ±0.3	±0.5 °	WEIGHT	A3	00779	C=2464043	-
MATERIAL	FINISH	CUSTOMER DRAWING			SCALE 3:1	SHEET 3 OF 3	REV A