





- 技术指标:
- 1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
 - 2. 额定电压: 150V AC, DC.
 - 3. 耐电压: 500V AC/minute.
 - 4. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
 - 5. 绝缘电阻: $\geq 500\text{M}\Omega$.
 - 6. 额定电流: 1A AC, DC.
- 材质:
- 1. 塑胶: PA66 白色

型号	CKT	A	B	C
HMT-DF1.25-10P-JK-A1	2*5	10.50	5.00	7.86
HMT-DF1.25-12P-JK-A1	2*6	11.75	6.25	9.11
HMT-DF1.25-14P-JK-A1	2*7	13.00	7.50	10.36
HMT-DF1.25-16P-JK-A1	2*8	14.25	8.75	11.61
HMT-DF1.25-18P-JK-A1	2*9	15.50	10.00	12.86
HMT-DF1.25-20P-JK-A1	2*10	16.75	11.25	14.11
HMT-DF1.25-22P-JK-A1	2*11	18.00	12.50	15.36
HMT-DF1.25-24P-JK-A1	2*12	19.25	13.75	16.61
HMT-DF1.25-28P-JK-A1	2*14	21.75	16.25	19.11
HMT-DF1.25-30P-JK-A1	2*15	23.00	17.50	20.36
HMT-DF1.25-32P-JK-A1	2*16	24.25	18.75	21.61
HMT-DF1.25-34P-JK-A1	2*17	25.50	20.00	22.86
HMT-DF1.25-36P-JK-A1	2*18	26.75	21.25	24.11
HMT-DF1.25-38P-JK-A1	2*19	28.00	22.50	25.36
HMT-DF1.25-40P-JK-A1	2*20	29.25	23.75	26.61
HMT-DF1.25-42P-JK-A1	2*21	30.50	25.00	27.86
HMT-DF1.25-44P-JK-A1	2*22	31.75	26.25	29.11
HMT-DF1.25-46P-JK-A1	2*23	33.00	27.50	30.36
HMT-DF1.25-48P-JK-A1	2*24	34.25	28.75	31.61
HMT-DF1.25-50P-JK-A1	2*25	35.50	30.00	32.86

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	X.°±5°	PART NO.	TITLE:	
.XX±0.25	.X.°±1°	HMT-DF1.25-NP-JK-A1	1.25 Pitch A型(DF13) 双排公头胶壳	
.XXX±0.15		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		MM
				SCALE
				SHEET
				N:A
				1/1