



ES5AB THRU ES5JB

SURFACE MOUNT GLASS PASSIVATED JUNCTION ULTRAFAST EFFICIENT RECTIFIER

Reverse Voltage: 50 to 600 Volts

Forward Current: 5.0 Amperes

Features

- Glass passivated cavity-free junction
- Ideal for surface mount automotive applications
- Ultrafast recovery time for high efficiency
- Built-in strain relief
- Easy pick and place
- Plastic package has Underwriters Laboratory Flammability
- Classification 94V-0
- Lead (Pb)-free component
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC
- High temperature soldering guaranteed: 260°C/10 seconds at terminals

Mechanical Data

Case: JEDEC SMB(DO-214AA) molded plastic body


TerMINals: solder plated, solderable per MIL-STD-750, method 2026

Polarity: color band denotes cathode end

Mounting Position: Any

Weight: 0.003ounce, 0.093 gram

SMB(DO-214AA)



Dimensions in inches and (millimeters)

Maximum Ratings & Thermal Characteristics

(Rating at 25°C ambient temperature unless otherwise specified, Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.)

		Symbols	ES5						Units
			AB	BB	DB	FB	GB	JB	
Maximum Repetitive Peak Reverse Voltage		V _{RRM}	50	100	200	300	400	600	Volts
Maximum RMS Voltage		V _{RMS}	35	70	140	210	280	420	Volts
Maximum DC Blocking Voltage		V _{DC}	50	100	200	300	400	600	Volts
Maximum Average Forward Rectified Current At T _L = 110°C		I _(AV)	5.0						Amps
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load		I _{FSM}	160					150	Amps
Maximum Instantaneous Forward Voltage at 3.0 A		V _F	0.95			1.25		1.7	Volts
Maximum DC Reverse Current At Rated DC Blocking Voltage	T _A = 25°C	I _R	5.0						μA
	T _A = 125°C		120						
Maximum Reverse Recovery Time(Note1)		T _{rr}	35						ns
Typical Junction Capacitance(Note2)		C _j	45						pF
Typical Thermal Resistance(NOTE3)		R θ JA	16						°C/W
Operating Junction and Storage Temperature Range		T _J , T _{STG}	-55 to +150						°C

Note: 1.Reverse Recovery Test conditions: $I_F = 0.5\text{A}$, $I_R = 1.0\text{A}$, $I_{RR} = 0.25\text{A}$.

2.Measured at 1MHz and applied reverse voltage of 4.0 Volts.

3.Thermal Resistance From Junction To Ambient P.C.B.Mounted On 0.2x0.2"(5.0x5.0mm)Copper Pad Areas.

Rating and Characteristic Curves ($T_A = 25^{\circ}\text{C}$ Unless otherwise noted)
ES5AB THRU ES5JB

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG.3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS




FIG.5-TYPICAL JUNCTION CAPACITANCE

