





- 技术指标 (Technical Index):
- 1. 工作温度 (Temperature range): $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
 - 2. 额定电压 (Rated voltage): 30V AC/DC .
 - 3. 额定电流 (Rated current): 0.5A AC/DC .
 - 4. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
 - 5. 耐压值 (Dielectricwithstanding voltage): 200V AC/minute .
 - 6. 绝缘电阻 (Insulation resistance): $\geq 100\text{M}\Omega$.
 - 7. 适用线规 (Apply to gauge): AWG#28~#32 (0. DO. 6mm MAX).

序号	品名	材质			
1	端子	Phosphor Bronze Bright tin plated			
GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X. ±0.50	±1°	PART NO.	TITLE:		
.X ±0.20		HMT-0.8-T	0.80 Pitch C型WTB公头端子		
.XX ±0.10		DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1