










电路示意图



开关安装面板



端子可选择:

端子类型	螺丝脚	小焊脚	6.5插脚	4.8插脚
简图				

技术要求:

- 开关参数: 16(10)A 250VAC;20(12)A 125VAC
- 操作温度: -25℃~+85℃
- 接触电阻: $\leq 0.02 \Omega$
- 绝缘电阻: $\geq 1000M \Omega$
- 耐压:
极与极(P-P):1500Vac 50Hz 1min 1.0mA
极与壳(P-H):1500Vac 50Hz 1min 1.0mA
- 扭柄换向力: 2 — 1 5 N
- 寿命: 5 0 0 0 0 次
- 材料: 电胶木和铜合金

01	--	第一次出图	LKH		2024. 04. 07
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)	绘图 (DRAW BY)	批核 (APP. BY)	日期 (DATE)
名称 (NAME)		功能 (Function) SPST:ON-OFF			
型号 (MODEL NO.)		CAX-KL-C101-YB-17.0JL		绘图 (DRAW BY)	批核 (APP. BY)
物料编号 (Material NO.)		比例 (SCALE)	1:1	日期 (DATE)	2024. 04. 07
公差除特别要求外, 均按此规定执行:X. =±0. 20, . X=±0. 15, . XX=±0. 1, <=±1°, 单位:mm (Tolerance unless otherwise specified:X. =±0. 20, . X=±0. 15, . XX=±0. 10, <=±1°, unit:mm)				