




技术指标 (Technical Index):

1. 工作温度 (Temperature range): $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$.
2. 额定电压 (Rated voltage): 250V DC/AC(rms) .
3. 额定电流 (Rated current): 3.0A AC, DC .
4. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值 (Dielectricwithstanding voltage): 800V AC/minute .
6. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.

序号	品名	材质
1	PHD2.0弯针WTB胶芯	PA66加玻纤 UL94 V-0 米色
2	PHD2.0弯针WTB端子	铜合金/表面 镀锡

GENERAL TOLERANCES
UNLESS SPECIFIED

X. ± 0.50	$\pm 1^{\circ}$
.X ± 0.20	
.XX ± 0.10	

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-PHD2.0-NP-WZ

TITLE:
PHD2.0 双排弯针WTB

DESIGN: James

CUSTOMER

SIZE
A4

CHED: Talen

SCALE

SHEET

APPD: Sophia

N:A

1/1