








技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}C \sim +105^{\circ}C$.
3. 额定电压: 150V AC/DC.
4. 额定电流: 1.0A AC/DC (AWG#28).
5. 接触电阻: $\leq 20m\Omega$ (Initial) per contact, $\leq 40m\Omega$ Change allowed.
6. 绝缘电阻: $\geq 500M\Omega$.
7. 耐压: 500V AC (Minute)



型号	CKT	A	B
HMT-DF1.25-10P-LTC	2*5	12.50	5.00
HMT-DF1.25-12P-LTC	2*6	13.75	6.25
HMT-DF1.25-14P-LTC	2*7	15.00	7.50
HMT-DF1.25-16P-LTC	2*8	16.25	8.75
HMT-DF1.25-18P-LTC	2*9	17.50	10.00
HMT-DF1.25-20P-LTC	2*10	18.75	11.25
.....			
HMT-DF1.25-50P-LTC	2*25	$(25*1.25)+6.25$	$(25*1.25)-1.25$



PCB WELDING DRAWING (TOLERANCE: ± 0.05)



4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式胶芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u"Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u"Min, 镀镍30u"Min
序号	名称	数量

GENERAL TOLERANCES
UNLESS SPECIFIED

.X $\pm$ 0.30

X. $^{\circ}$ $\pm$ 5 $^{\circ}$

.XX $\pm$ 0.25

.X. $^{\circ}$ $\pm$ 1 $^{\circ}$

.XXX $\pm$ 0.15

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

HMT-DF1.25-NP-LTC

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:
1.25 Pitch A型(DF13)

双排立式带柱业务图

CUSTOMER

SCALE

N:A

SIZE
A4

UNITS
MM

SHEET
1/1