




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.18	阿树



Recommended P.C.B Layout
General Tolerance±0.05




- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:3A AC/DC
 - Withstanding Voltage:800V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤20mΩ
 - Sheel:PA4T UL94-V0
 - PIN:C2680 Tin

Poles	Dimensions(mm)	
	A	B
2X02	2.00	6.00
2X03	4.00	8.00
2X04	6.00	10.00
2X05	8.00	12.00
2X06	10.00	14.00
2X07	12.00	16.00
2X08	14.00	18.00
2X09	16.00	20.00
2X10	18.00	22.00
2X11	20.00	24.00
2X12	22.00	26.00
2X13	24.00	28.00
2X14	26.00	30.00
2X15	28.00	32.00
2X16	30.00	34.00
2X17	32.00	36.00
2X18	34.00	38.00
2X19	36.00	40.00
2X20	38.00	42.00


PART NO.:

X2006 W R-2x06-4T SN
① ② ③ ④ ⑤ ⑥


- ①Series No
②Category:W-Wafer
③Welding Board Angle:R-Straight 90°
④Row No.Pin No:2xXX-2x02~2x20Pin
⑤Material:4t-PA4t UL94V-0
⑥Planting Category:SN-Bright Tin Plated




6P




8~10P



12~18P



20~40P



6P~14P Without Guideway
16P~40P With Guideway
Scale: 1/0.5

X2006WR-2x06-4TSN	PA4T UL 94V-0	X2006H
PART NO	Material	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	UNIT: mm/in
SIZE: A4	

MODEL TYPE: 2.00mm Crimp Style Connectors
PART NO.: X2006WR-2x06-4TSN
DWG NO.: X-X2006WR-2x06-4TSN