





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.06	阿树




Contact Rating:50mA,12V DC
触点额定值: 50mA, 12V DC
Contact Resistance:100MΩ max
接触电阻: 最大100MΩ
Insulation Resistance:100mΩ min.500V DC
绝缘电阻: 100mΩ最小500V DC

Dielectric Strength:250V AC/1minute
介电强度: 250V AC/1分钟
Operating Temp:-25℃~+80℃
工作温度: -25℃~+80℃
Storage Temp:-30℃~+80℃
储存温度: -30℃~+80℃
Life: 100000
寿命: 100000



P.C.B LAYOUT



CIRCUIT DIAGRAM

PAPT NO	TS-7473-B
Operating Force	B:160gf

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: TACT SWITCH
CHECKED		UNIT: mm/in	PART NO.: TS-7473-B
APPROVED		SIZE: A4	DWG NO.: TS-7473-B