







- NOTES:
- MATERIAL:
HOUSING: LCP UL94V-0, BLACK
CONTACT: C5210R-EH, T=0.20mm
 - DURABILITY TEST: 100 CYCLES MIN.
 - SPECIFICATION:
DIELECTRIC STRENGTH: AC 300V/MINUTE
INSULATOR RESISTANCE: 500 Mohm MIN
CONTACT RESISTANCE: 40 mohm Max.
OPERATING TEMPERATURE: -40° ~ +85°



			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称 TITLE	SPF (20Pin CONN)	版 本 REV.	A
			X. XX	±0.20	批 准				
			X. XXX	±0.10	APPROVAL				
			Angle	±3.0°	比 例				
1	初版发行		SCALE		投 影	产品料号 PART NO.	HC-SFP-20P	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE			Projection	材 料 MATERIAL		页 次 SHEET	1/1