



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.08.29	阿树



P.C.B Layout





■SPECIFICATIONS

- Voltage rating:50V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥100MΩ
- Contact resistance:≤20mΩ

PART NO.:

X1011 W V S-2x10-9T SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.WELDING Way:S-SMT
- 5.Row No.Pin No:2xXX-2x02~2x25Pin
- 6.Material:9T-PA9T UL94V-0
- 7.Plating:SN-Bright tin plating
V01-All Gold Flash



Poles	Dimensions/mm			Poles	Dimensions/mm		
	A	B	C		A	B	C
2x02	1.00	4.30	2.50	2x11	10.00	13.30	11.50
2x03	2.00	5.30	3.50	2x12	11.00	14.30	12.50
2x04	3.00	6.30	4.50	2x14	13.00	16.30	14.50
2x05	4.00	7.30	5.50	2x15	14.00	17.30	15.50
2x06	5.00	8.30	6.50	2x16	15.00	18.30	16.50
2x08	7.00	10.30	8.50	2x18	17.00	20.30	18.50
2x09	8.00	11.30	9.50	2x20	19.00	22.30	20.50
2x10	9.00	12.30	10.50	2x25	24.00	27.30	25.50

X1011WVS-2x10-9TSN	PA9T UL 94V-0	Phosphor Bronze	Tin-Plated	X1011T
X1011WVS-2x10-9TV01			Gold-Flash	
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.0mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X1011WVS-2x10-9TSN
APPROVED		SIZE: A4	DWG NO.: X-X1011WVS-2x10-9TSN

SCALE	PAGE	REVISION
N/A	1/1	A1