





6		7		8	
REV	DESCRIPTION OF CHANGE	REVIEWED BY	ISSUE DATE		
A	FIRST ISSUE	X.YAN	2025-07-16		



NOTE:

1. Material:
HOUSING: HIGH TEMPERATURE LCP, BLACK, UL 94 V-0 FLAME RETARDANT.
2. TERMINAL : NICKEL COPPER ALLOY
PLATING SPEC AS BELOW:

CONTACT AREA PLATE NICKEL 1.27um MIN, PLATE Gold 0.76um MIN
SOLDER AREA PLATE NICKEL 1.27um MIN, PLATE MATT TIN 1.5~4.5um
3. ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING: 1AMPERE
VOLTAGE RATING: 30V DC
CONTACT RESISTANCE: 50 MILLOHMS MAX
DIELECTRIC WITHSTANDING VOLTAGE: 300V AC
4. ENVIRONMENT
OPERATION TEMPERATURE: -40° C TO 85° C



TITLE □SFP112 1X1 CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. OSFP 2324869-2-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1"	SCALE: 1:1	SHEET:1/2	REV:A
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5"			
			.XXX±0.10				

