



NOTES 注释:

1. MATERIAL材料:

1.1 HOUSING外壳: THERMOPLASTIC, HIGH TEMP.,
UL94V-0;

COLOR: SEE PART NO..

1.2 CONTACTS触点: COPPER ALLOY.

2. FINISH饰面:

2.1 CONTACT触点:

SELECTEIVE GOLD PLATING ON CONTACT AREA.
100μ"MIN. MATTE TIN PLATING ON SOLDER TAILS
50μ" MIN. NICKEL UNDERPLATING OVERALL.

X3157 W S - 36 - 9T V15

① ② ③ ④ ⑤ ⑥

①Series Nunber

②Terminal form: W-Wafer

③Welding Board Angle : Straddle

④No.of Pins: 36~164 Pin

⑤Plastic material: PA9T /PA46 UL94V-0

⑥Contact Plating:V15-Gold 15u"
V30-Gold 30u"



DIMENSIONS				
POSITION	A±0.25	B±0.20	C±0.20	D±0.20
36	25.00	7.65	6.00	23.00
64	39.00	21.65	20.00	37.00
98	56.00	38.65	37.00	54.00
164	89.00	71.65	70.00	87.00

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB


XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X3157WS-36-9TV15
CHKD	UNIT: mm/in	DWG NO.: X-X3157WS-36-9TV15
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0




RECOMMENDED PCB LAYOUT
PCB TOLERANCE: ±0.05

DIMENSIONS					
POSITION	A	E	J	F	"K"
36	6	23	9.5	8.15	B17
64	20	37	23.5	22.15	B17,B31
98	37	54	40.5	39.15	B17,B31,B48
164	70	87	73.5	72.15	B17,B31,B48,B81



I/O PANEL DIRECTION
PRIMARY (COMPONENT) SIDE







SECONDARY (SOLDER) SIDE
PCI-E ADD-IN CARD EDGE-FINGER DIMENSION

6. NO TIE BAR PERMITTED FROM CARD EDGE TO
LEADING EDGE OF PAD FOR PINS A1 AND "K"
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X3157WS-36-9TV15
CHKD		UNIT: mm/in	DWG NO.: X-X3157WS-36-9TV15
APPD		SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1/1 A0



DIMENSIONS	
POSITION	F
36	20.4
64	34.4
98	51.4
164	84.4

ASSEMBLY WITH CAP CONDITION

					ANGLAR	±5°		DSND		SCALE: N/A	MODEL TYPE:
Δx					L ≤ 4	±0.2		DWN		VIEW: 	PART NO.:
Δx					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	X3157WS-36-9TV15
Δx					16 < L ≤ 63	±0.4		APPD		SIZE: A4	DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5		XKB INDUSTRIAL PRECISION CO., LIMITED			X-X3157WS-36-9TV15
REVISIONS						UNSPECIFIED TOLERANCES		WEIGHT	SHEET	REVISION	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn									1/1	A0	