



产品编码 P/N	PSCLAQ0905 Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	共模线性滤波器	测试频率 TEST FREQUENCY	参考规格书内定义

客户名称

Customer

客户编码

Customer P/N

产品系列

Series

共模线性滤波器

Common Mode Linear Filter

产品编码

Supply P/N

PSCLAQ0905 Series

发版号

Version

A3.0

承认日期

Endorsement Date

2026-7-5

备注

Note

谱罗德电子科技（深圳）有限公司 PuLuoDe Electronic Technology (Shenzhen) Co. LTD	
制作 APPROVED	Ben
审查 CHECKED	Yuki
确认 PREPARED	Peter

客户承认

Customer Approval

客户签章



谱罗德电子科技（深圳）有限公司

PuLuoDe Electronic Technology (Shenzhen) Co., LTD

深圳市宝安区石岩三联工业区B栋311

更多规格请访问谱罗德官方网站
下载或者扫描二维码通过微信小程序获取

<http://www.prodtech.cn/>

A3.0

修订记录

REVISION RECORD

RoHS

compliant

REACH

compliant

产品编码 P/N	PSCLAQ0905 Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302	
产品系列 Series	共模线性滤波器	测试频率 TEST FREQUENCY	参考规格书内定义	

Version	REVISION ITEM	BEFORE REVISION	AFTER REVISION	DATE
A3.0				2026-7-5

谱罗德

PROD

谱罗德电子科技（深圳）有限公司

PuLuoDe Electronic Technology (Shenzhen) Co., LTD

深圳市宝安区石岩三联工业区B栋311

更多规格请访问谱罗德官方网站
下载或者扫描二维码通过微信小程序获取

<http://www.prodtech.cn/>

产品编码 P/N	PSPOCI3225C Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	POC电感	测试频率 TEST FREQUENCY	参考规格书内定义

产品特点


Features

- ☐ 产品薄，尺寸小，额定电流最大可达1.6A
Low profile, Small size and the rated current up to 1.6A
- ☐ 适用于10KHz~500MHz频率的滤波
EMI suppression range: 10KHz~500Mhz
- ☐ SMD结构便于SMT生产自动化贴片
SMD structure is convenient for SMT production automation patch



电路图

Schematic



- ◎ 电感内置两组线圈
Inductor Contents 2 Sets of Coil

编码解释

Code interpretation

P S C L A Q	0 9 0 5	-	X X X	Y
<u>类别码</u>	<u>尺寸系列</u>		<u>电感值</u>	<u>精度</u>
Category code	Dimension		Inductance	Tolerance


- ◎ 规格参数基于环境温度25℃取得
All test Data is referenced to 25℃ ambient
- ◎ 电感工作环境温度：-40℃ ~ 105℃
Operating temperature range -40 °C to +105 °C
- ◎ 加载额定电流会使电感温度上升大约 40℃ (电感初始温度+上升温度=电感最终温度)
Typical Heat Rating DC Current would cause an approximately ΔT of 40℃
- ◎ 务必考虑最终的产品设计，元器件布局，线路板走线，以及使用环境过程中，电感最终温度不得超过105℃
The operating temperature of inductance do not exceed 105℃
- ◎ 使用电感时，请查阅最后一页注意事项
The announcements is on last page
- ◎ 规格书中给出的参数精度为“+∞”，则意味着该规格不规定该参数的上限；参数精度为“Ref”“Typ”时，则该值仅做参考，无明确的正负公差
∞=unlimited, Ref or Typ=It is merely a reference value and does not have positive or negative tolerance.



产品编码 P/N	PSCLAQ0905 Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	共模线性滤波器	测试频率 TEST FREQUENCY	参考规格书内定义

封装尺寸
Dimension (mm)

推荐的焊盘尺寸
Recommened Land Pattern



系列 Series	封装尺寸 Dimension								
	A	B	C	D	H	E	F	L	W
0905	9.2±0.3	6.0±0.3	5.0±0.3	1.4 Max	0.8±0.2	2.54 Ref	5.7 Ref	1.8 Ref	1.0 Ref

编码解释

Code interpretation

PSCLAQ	0905	-	102	Y
类别码	尺寸系列		阻抗值	精度
Category code	Dimension		Impedance	Tolerance

电气参数


Electrical Characteristics

产品编码 P/N	@ 25 °C Ambient Temperture							
	感值值 (L)	精度 Tolerance	测试频率 Test Frequency	DCR	额定电流 Rated Current	滤波范围 Frequency Range	额定电压 Rated Voltage	峰值阻抗 Peak Impedance
	N1=N2			Ω	mA			Ω@MHZ
	μH	±	KHZ	Max	ΔT≈40℃	MHZ(Ref.)	Vdc	Ref
PSCLAQ0905-100N	10	30%	1KHZ/ 0.1V	0.08	1600	10~500	80	1.2KΩ@90MHz
PSCLAQ0905-250N	25	30%		0.16	1000	5~300	80	1.8KΩ@60MHz
PSCLAQ0905-400N	40	30%		0.25	900	5~300	80	2.9KΩ@40MHz
PSCLAQ0905-500N	50	30%		0.32	800	5~100	80	3.3KΩ@20MHz
PSCLAQ0905-251Y	250	50%	100KHZ /5mV	0.13	1200	0.5~100	80	1.5KΩ@20MHz
PSCLAQ0905-471Y	470	50%		0.14	1100	0.5~100	80	2.5KΩ@20MHz
PSCLAQ0905-501Y	500	50%		0.15	1000	0.5~100	80	2.6KΩ@17MHz
PSCLAQ0905-102Y	1000	50%		0.31	800	0.05~100	80	2.7KΩ@10MHz
PSCLAQ0905-202Y	2000	50%		0.42	600	0.05~50	80	4.2KΩ@1MHz
PSCLAQ0905-472Y	4700	50%		0.9	400	0.05~30	80	17KΩ@1MHz
PSCLAQ0905-652Y	6500	50%		1.05	300	0.01~30	80	17.5KΩ@1MHz

产品编码 P/N	PSCLAQ0905 Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	共模线性滤波器	测试频率 TEST FREQUENCY	参考规格书内定义

特性曲线


Performance Curves



产品编码 P/N	PSPOCI3225C Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	POC电感	测试频率 TEST FREQUENCY	参考规格书内定义

焊接温度（推荐）

Recommended Classification Wave Soldering Profile



Classification Reflow Soldering Profile:

Profile Feature	Item	Value
Preheat Temperature Min	Ts min	150 °C
Preheat Temperature Max	Ts max	200 °C
Preheat Time ts from Ts min to Ts max	ts	60 - 120 seconds
Ramp-up Rate (TL to TP)		3 °C/ second max.
Liquidous Temperature	TL	217 °C
Time tL maintained above TL	tL	60 - 150 seconds
Peak package body temperature	Tp	Tp ≤ Tc, see Table below
Time within 5°C of actual peak temperature	t p	20 - 30 seconds
Ramp-down Rate (TP to TL)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

Package Classification Reflow Temperature (Tc):

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly Package Thickness < 1.6 mm	260°C	260°C	260°C
PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm	260°C	250°C	245°C
PB-Free Assembly Package Thickness > 2.5 mm	250°C	245°C	245°C


* 参考标准: IPC/ JEDEC J-STD-020E refer standard to: IPC/ JEDEC J-STD-020E



产品编码 P/N	PSPOCI3225C Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	POC电感	测试频率 TEST FREQUENCY	参考规格书内定义

可靠性实验

RELIABILITY TESTING

项目/Item	方法/Method
Operating Temperature	- 40 to +105 °C (Contain Heating coil)
Appearance Inspection	No external defects by visual inspection
Terminal Strength	 After soldering , between copper plaet and terminals of coils , push in two directions of X , Y with standing 10N(1.02kg) for10+/-2 sec. Terminal should not peel off. (Refer to figure at right)
Heat endurance of reflow soldering	
Insulating resistance	Preheating: 150±10°C for 60 seconds Soldering: 245±5°C dwell for 5+/- 0.5 second
Dielectric Strength	Over 10 MΩ at 50V D.C . between wire and core
Temperature characteristics	Apply at 0.5KV 1mA for 3S between wire and core
Humidity characteristics	Inductance coefficient (0~2,000) × 10 / °C(- 40~ + 105 °C)
	Inductance deviation within ± 10% , after 96 hours in 90~95% relative humidity at 40 ± 2 °C and 1 hours drying under normal condition

A test is made under the above mentioned condition , and it is kept for 2 hours in the normal




产品编码 P/N	PSCLAQ0905 Series	测试设备 TEST INSTRUMENT	Keysight:E4991B Chroma:16502 3302
产品系列 Series	共模线性滤波器	测试频率 TEST FREQUENCY	参考规格书内定义

載帶卷盤尺寸 : (mm)

Packing Dimension

MPQ	A	B	C	D	P	P1	W	L
1000pcs/卷盤	330 Typ	21 Ref	13 Ref	18 Ref	12 Ref	4 Ref	12 Ref	前后预留约30空格




載帶剥离力:

Typical Pulling Force

对上盖带施加力: 20g~120g内即可与下载带剥离

Tape Peeling off force: 20g~120g




装箱数量:

Package Quantity

最小包装

MPQ


1000pcs/Reel



内盒

Middle box


20000pcs/ Middle box



外箱

Outer box

60000pcs/ Outer box



© 实际出货过程, 依据客户需求状况的不同, 包装数量会有变化, 最终的包装数量请参照实际出货包装

In the actual delivery process, the package quantity will change according to the different customer demands. Please refer to the actual shipment quantity for the final package quantity



注意事项

使用本产品时，请注意以下事项

- ◎ 产品保存期限为12个月，保存条件：温度5~40℃，湿度10~75%RH以内，超过保存期限可能会使元器件电极发生氧化，存储标准可参照：IEC_61760-2-2021
This components storage life is 12 months, Storage Temperature: TEMP.5~40℃; RH10%~75%. Please use this components within the warranty period. refer standard to: IEC_61760-2-2021
- ◎ 请勿在极端环境下使用和保存（高盐，强酸，强碱，强辐射等）。
Do not use this component in special environments, such as high salt content, strong acid, strong alkali, strong corrosion and other special environments.
- ◎ 元器件焊接前,请进行预热,预热与焊接温度之间温差建议控制在150℃以内;焊接标准参考：EN61760-1:2006
Please preheat the product before welding; it is recommended to control the preheating temperature and welding temperature within 150℃. refer standard to: EN61760-1:2006
- ◎ 元器件焊接后需重新拆卸焊接修正时，请遵循规格书规定的条件范围；过高的加热温度以及反复的拆卸可能会导致元器件失效。
When repairing this component, the temperature used for disassembly should not exceed the datasheet limit and do not disassemble it frequently to prevent damage to the component.
- ◎ 请勿用清洗剂、丙酮等腐蚀性液体接触该元器件，这可能会侵蚀元器件本体以至于失效。
Do not use acetone or other corrosive liquids to contact this component or it will cause it to fail.
- ◎ 元器件焊接到线路板后，请注意不可因线路板整体变形或局部变形而施加给电感剩余应力，这可能会导致元器件脱落、破损失效。
When this component is soldered to the circuit board, you need to pay attention to the stress applied to it by the PCB, which may cause it to fall off or damaged fail.
- ◎ 元器件通电后温度会随电流的增大而上升，设计时请务必考虑留有余量。
Self heating (Rated Current or Irms) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- ◎ 过高的静电会损坏该元器件，请注意静电防护。
Too high static electricity will cause permanent damage to the product, please pay attention to electrostatic protection.
- ◎ 本元器件作为磁性产品，设计时请务必考虑周边元器件与本产品可能产生的耦合效应影响。
This magnetic component needs to be considered for coupling effects in the application.
- ◎ 谱罗德并不能完全掌握或熟悉客户的特定应用以及要求，贵司有责任和义务验证此元器件以及元器件规格书中的描述是否满足于贵司的设计要求；需要指出是：即使按照现有的技术标准操作，该元器件依然有几率在典型寿命结束前发生故障，谱罗德强烈建议贵司对于该元器件在一些典型的严苛应用中，例如安规产品，工业产品、医疗产品、车载产品、航空/航天等产品应用，对于该元器件可能存在的失效情况做适当的冗余设计，以此避免该元器件在失效时造成严重后果；特别提醒：对于特定的应用对象谱罗德强烈要求贵司同谱罗德取得书面的许可，否则谱罗德不予承担元器件失效带来的任何责任，特定对象包括且不限于：车用，航空航天，安规产品，军用以及贵司对元器件有严苛要求的产品。
PROD cannot fully understand and be familiar with customers' specific applications and requirements. Your company has the responsibility and obligation to verify whether the components and the description in the component specification meet your design requirements. Special reminder: Even if operated in accordance with existing technical standards, this component still has a chance of failure before the end of its typical life. PROD strongly recommends that your company make appropriate redundant designs for possible failure situations of this component in some typical harsh applications, such as safety products, industrial products, medical products, automotive products, aviation/aerospace products, etc., so as to avoid serious consequences when the component fails.
PROD Requirements: For specific application item, PROD strongly requires your (or company) to obtain written permission from PROD, otherwise PROD will not bear any responsibility for component failure. Specific item list include but are not limited to: automotive, aerospace, safety products, military and products that your company has strict requirements on components.



谱罗德电子科技（深圳）有限公司

PuLuoDe Electronic Technology (Shenzhen) Co., LTD

深圳市宝安区石岩三联工业区B栋311

更多规格请访问谱罗德官方网站
下载或者扫描二维码通过微信小程序获取

<http://www.prodtech.cn/>

